






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
K2		REVISED PER ECO-09-021826	07JAN10	KK	AEG
K3		REVISED PER ECO-20-013196	21SEP20	RK	MZ
K4		REVISED PER ECO-20-013409	23SEP20	RK	MZ



△ 2.54µm [.000100] MIN NICKEL OVER
2.54µm [.000100] MIN COPPER.

△ 2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



ASSEMBLED VIEW

2	OBSOLETE	YES	7.62–11.43 [.300–.450]	BULK	–	STAINLESS STEEL	213931–9–
	OBSOLETE	YES	11.05–13.84 [.435–.545]	INDIVIDUAL	–	STAINLESS STEEL	213931–8–
2	OBSOLETE	YES	11.05–13.84 [.435–.545]	BULK	1	ZINC	213931–7–
	OBSOLETE	NO	11.05–13.84 [.435–.545]	INDIVIDUAL	1	ZINC	213931–6
2		YES	7.62–11.43 [.300–.450]	INDIVIDUAL	1	ZINC	213931–5
	OBSOLETE	NO	11.05–13.84 [.435–.545]	INDIVIDUAL	1	ZINC	213931–4–
		YES	11.05–13.84 [.435–.545]	INDIVIDUAL	1	ZINC	213931–3
		YES	7.62–11.43 [.300–.450]	INDIVIDUAL	–	STAINLESS STEEL	213931–2
		YES	11.05–13.84 [.435–.545]	INDIVIDUAL	–	STAINLESS STEEL	213931–1
		RECEPTACLE HOUSING	CABLE RANGE DIA	PACKAGING	FINISH	MATERIAL	PART NUMBER
					JACKSCREWS		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. BROCKWAY 12DEC95	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK C. DORWART 12DEC95		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. MCALONIS 13DEC95	NAME CONNECTOR KIT, UNASSEMBLED, RECEPTACLE, 34 POSITION, M SERIES	
0 PLC ± - 1 PLC ± - 2 PLC ± 0.76 [.030] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC	RESTRICTED TO	
MATERIAL SEE CALLOUTS		APPLICATION SPEC	SIZE A1	
FINISH SEE CALLOUTS		WEIGHT	DRAWING NO 00779	
CUSTOMER DRAWING		SCALE 2:1	SHEET 1 OF 1	
			REV K4	