







- | | | |
|---------------------|---------------|-------------|
| 2 | Au PLATING | 2170610-3 |
| 9 | Pd-Ni PLATING | 2170610-2 |
| 2 | Au PLATING | 2170610-1 |
| CONTACT
FINISHED | DESCRIPTION | PART NUMBER |


4805 (3/13)

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



SECTION V-V




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: KEVIN DING 21OCT13	 TE Connectivity	
		CHK: JASON YANG 21OCT13		
DIMENSIONS: mm		APVD: JASON YANG 21OCT13	NAME	CAGE AND CONNECTOR ASSEMBLY, WITH EMI GASKET, 2X3, THERMAL FOOTPRINT, ZQSP+STACKED
		PRODUCT SPEC		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	108-60102	SIZE	CASE CODE
		APPLICATION SPEC		
MATERIAL SEE NOTE 1	FINISH SEE NOTE 2	114-60015	DRAWING NO	RESTRICTED TO
		WEIGHT		
		A100779C=2170610		-
		CUSTOMER DRAWING		SCALE 4:1 SHEET 2 OF 4 REV A



RECOMMENDED PC BOARD LAYOUT
COMPONENT SIDE OF BOARD
PCB TOLERANCE: ± 0.05

4805 (3/13)

REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN
-	-	SEE SHEET 1	-	-



KEEPOUT AREAS
COMPONENT SIDE OF BOARD

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: KEVIN DING 210CT13	TE Connectivity	
		CHK: JASON YANG 210CT13		
DIMENSIONS:		APVD: JASON YANG 210CT13	NAME: CAGE AND CONNECTOR ASSEMBLY, WITH EMI GASKET, 2X3, THERMAL FOOTPRINT, ZQSFP+STACKED	
mm		PRODUCT SPEC		
		108-60102	SIZE: 114-60015	
		APPLICATION SPEC		
		114-60015		
		FINISH		
MATERIAL: SEE NOTE 1		WEIGHT: -	A100779C=2170610	
SEE NOTE 2		CUSTOMER DRAWING		
		SCALE: 4:1	SHEET: 4 OF 4	REV: A