

S42F1C-P05MPH0-900S
series_f, type_s4





General information

| | |
|-------------------|---------------------|
| Part number | S42F1C-P05MPH0-900S |
| Termination | solder |
| Size | 2 |
| Locking principle | push |
| Coding | 1_halfshell |
| Cable Diameter | cable_mini_90 |
| Cable outlet | bend_relief |



Illustrations may differ from original product.
Dimensions, unless otherwise specified, in mm.



Contact insert description

| | |
|----------------------|--------|
| Number of contacts | 5 |
| Contact type | pins |
| Contact diameter | 13mm |
| Insulator material | peek |
| Wire cross section | 20_awg |
| Termination | solder |
| Termination diameter | 11mm |

reverse_gender_on_request

Technical information

| | | |
|--|----------|---------------|
| Max. creepage and air clearance distance | 12_mm | 11_mm |
| Nominal current single contact | 12_a | iec_60512_5_2 |
| Nominal current insert | 9 A | vde_0298_4 |
| Test voltage | 15_kv_ac | sae_13441 |

safety_text

Mechanical and environmental data

| | |
|-----------------------|----------|
| Degree of protection* | ip68 |
| Operating temperature | 40_120_c |
| Mating cycles | 5000 |

mated

Material and surface treatments

| | |
|---------|---------------|
| Housing | m_chrome |
| Contact | cu_alloy_gold |

safety_text_2
ul_text
illustrative_text