



LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
AA	00		A9	ADD NEW PARTS	15OCT2014	OL	SZ	
			A10	ECR-15-001425	22DEC2014	SZ	SZ	






- HOUSING: GLASS FILLED LIQUID CRYSTAL POLYMER, COLOR: BLACK, UL 94 V-O RATED
SIGNAL CONTACT: PHOSPHOR BRONZE
SIGNAL OVERMOLD: GLASS FILLED POLYESTER
POWER CONTACT: COPPER ALLOY
- SIGNAL CONTACT: 0.00127mm MIN NICKEL ALL OVER,
MATING AREA: 0.00076mm MIN GOLD OR 0.00008mm MIN GOLD OVER
0.00076mm MIN PALLADIUM-NICKEL,
TAIL AREA: 0.0005mm MIN MATTE TIN

POWER CONTACT: 0.00127mm MIN NICKEL ALL OVER,
MATING AREA: 0.00076mm MIN GOLD OR 0.00008mm MIN GOLD OVER
0.00076mm MIN PALLADIUM-NICKEL,
TAIL AREA: 0.0005mm MIN MATTE TIN
- CONTACT MATING AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT,
TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995
- THIS CONNECTOR EMPLOYS UL RECOGNIZED Z-PACK 2mm HM SIGNAL CONTACTS
- DATUMS AND BASIC DIMENSIONS TO BE ESTABLISHED BY CUSTOMER
- SEE APPLICATION SPEC 114-13215 FOR PLATED THROUGH HOLE INFORMATION
- SEE CUSTOMER DRAWING 1926730 OR 1926732 FOR MATING CONNECTOR
- UNPLATED HOLES

12	10	1	1	18.95	23.74	10S X 2P	1-1892787-4
12	15	1	2	20.95	25.74	15S X 2P	1-1892787-3
12	25	1	4	24.95	29.74	25S X 2P	1-1892787-2
120	35	19	6	78.45	83.24	35S X 20P	1-1892787-1
108	35	17	6	72.95	77.74	35S X 18P	1-1892787-0
48	20	7	3	39.45	44.24	20S X 8P	1892787-9
60	25	9	4	46.95	51.74	25S X 10P	1892787-6
24	20	3	3	28.45	33.24	20S X 4P	1892787-4
24	10	3	1	24.45	29.24	10S X 4P	1892787-2
F PLC	E PLC	D SPACES	C SPACES	DIM B	DIM A	NO OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	28OCT2011		 TE Connectivity						
				CHK	28OCT2011								
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	28OCT2011		NAME						
mm				SUNY ZHAO									
		0	PLC	±	PRODUCT SPEC 108-2325 APPLICATION SPEC 114-13215			RECEPTACLE ASSEMBLY, VERTICAL, PASSIVE GUIDE, SIGNAL/POWER, SCREW MOUNT OPTION, MINIPAK HDL					
		1	PLC	±									
		2	PLC	±0.13									
		3	PLC	±									
		4	PLC	±	SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO		
		ANGLES	±										
MATERIAL		FINISH		WEIGHT		A100779		©=1892787					
SEE NOTE 1		SEE NOTE 2		-		Customer Drawing		SCALE 2:1		SHEET 1 OF 3		REV A10	

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AA	00	-					
		-	SEE SHEET 1		-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN: ORANDO L1 28OCT2011
CHK: SUNY ZHAO 28OCT2011
APVD: SUNY ZHAO 28OCT2011

NAME: RECEPTACLE ASSEMBLY, VERTICAL, PASSIVE GUIDE, SIGNAL/POWER, SCREW MOUNT OPTION, MINIPAK HDL

DIMENSIONS:

mm

0 PLC ±
1 PLC ±
2 PLC ±0.13
3 PLC ±
4 PLC ±
ANGLES ±
FINISH

TOLERANCES UNLESS OTHERWISE SPECIFIED:

MATERIAL: SEE NOTE 1

NOTE 2

Customer Drawing

PRODUCT SPEC: 108-2325

APPLICATION SPEC: 114-13215

WEIGHT: -

SIZE: A1

CAGE CODE: 00779

DRAWING NO: 1892787

RESTRICTED TO: -

SCALE: 2:1

SHEET: 2

OF: 3

REV: A10

