

# HUBER+SUHNER® DATA SHEET

## Coaxial PCB Connector: 82\_BMA-50-0-1/111\_N

Rev.: D



### Description

Straight PCB jack

### Interface Standards

IEC 60169-33\_MIL-STD-348A/321



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

#### Mechanical Data

Board mounting type	through holes
Weight	0.001 kg

#### Environmental Data

Operating Temperature	-65 °C to 125 °C
2002/95/EC (RoHS)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

#### Related Documents

Outline drawing	DOU-00013034
Catalogue drawing	DCA-00013236

#### Ordering Information

Single package	82_BMA-50-0-1/111_NE
----------------	----------------------

#### Remarks

PCB connector without stand-offs

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

#### WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG

RF Technology

9100 Herisau, Switzerland

Phone +41 (0)71 353 41 11

Fax +41 (0)71 353 45 90

[www.hubersuhner.com](http://www.hubersuhner.com)

**HUBER+SUHNER – Excellence in Connectivity Solutions**