

## SOD-323 Fast Switching Diodes

### Features

- $I_{F(AV)}=200\text{mA}$
- Power Dissipation of 250mW
- Fast switching speed
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260°C

### Applications



For use in low voltage high frequency circuit signals.

### Mechanical Data

- Case: SOD-323  
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant, halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750, Method 2026
- Polarity: Cathode line denotes the cathode end


### Function Diagram

Marking:  
BAV19WS:A8  
BAV20WS:T2  
BAV21WS:T3



**Reverse Voltage**  
120 V/200V/250V  
**Forward Current**  
0.2 Ampere

SOD-323







### Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	BAV19WS	BAV20WS	BAV21WS
Maximum repetitive peak reverse voltage	$V_{RRM}$	V	120	200	250
Maximum RMS Voltage	$V_{RMS}$	V	100	150	200
Reverse Breakdown voltage @ $I_r=100\mu\text{A}$	$V_{(BR)R}$	V	120	200	250
Maximum Average Forward Rectified Current	$I_{F(AV)}$	mA	200		
Repetitive peak forward current	$I_{FRM}$	mA	625		
Non-Repetitive Peak forward surge current @ $t_p=1.0\mu\text{s}$	$I_{FSM}$	A	2.5		
Non-Repetitive Peak forward surge current @ $t_p=1.0\text{s}$			0.5		
Power Dissipation	$P_d$	mW	250		
Storage temperature	$T_{stg}$	°C	-55 ~ +150		
Junction temperature	$T_j$	°C	-55 ~ +150		
Typical thermal resistance	$R_{\theta J-A}$	°C /W	500		

● **Electrical Characteristics** (Ta=25°C Unless otherwise noted)

PARAMETER	TEST CONDITIONS	SYMBOL	UNIT	BAV19WS	BAV20WS	BAV21WS
Maximum instantaneous forward voltage	I <sub>F</sub> =100mA	V <sub>F</sub>	V	1.0		
	I <sub>F</sub> =200mA			1.25		
Reverse Leakage Current	V <sub>R</sub> =V <sub>RMS</sub>	I <sub>R</sub>	nA	100		
Total capacitance	V <sub>R</sub> =0V, f=1MHz	C <sub>T</sub>	pF	5.0		
Maximum reverse recovery time	I <sub>F</sub> =I <sub>R</sub> =30mA, I <sub>rr</sub> =0.1×I <sub>R</sub> , R <sub>L</sub> =100Ω	T <sub>rr</sub>	ns	50		

● **Ratings And Characteristics Curves** (Ta=25°C Unless otherwise specified)



# BAV19WS THRU BAV21WS

FAST SWITCHING DIODES

## ● Ordering Information

PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
SOD-323	R1	0.0048	3000	45000	180000	7"

## ● Package Outline Dimensions (SOD-323)

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	1.60	1.80	0.063	0.071
B	0.25	0.40	0.010	0.016
C	2.30	2.80	0.091	0.110
D	0.80	1.10	0.031	0.043
D <sub>1</sub>	0.80	0.90	0.031	0.035
E	1.20	1.40	0.047	0.055
F	0.08	0.18	0.003	0.007
L	0.475REF		0.019REF	
L <sub>1</sub>	0.25	0.40	0.010	0.016
H	-	0.14	-	0.006

## ● Suggested Pad Layout

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
X	0.65	0.75	0.026	0.030
Y	0.65	0.75	0.026	0.030
Z	2.10	2.20	0.084	0.088