

1.Features

- Unidirectional ESD protection of two lines
- ESD protection up to 30 kV
- Low diode capacitance: $C_d=17\text{pF}$
- IEC 61000-4-2; level 4 (ESD)
- Max. peak pulse power: $P_{pp}=160\text{W}$
- IEC 61000-4-5 (surge); $I_{pp}=2.5\text{A}$
- Low clamping voltage: $V_{CL}=55\text{V}$
- AEC-Q101 qualified
- Ultra low leakage current: $\text{IRM} \leq 1\mu\text{A}$


3.Machanical Data

- SOT-23 package
- Flammability Rating: UL 94V-0
- Packaging: Tape and Reel

2.Applications

- Computers and peripherals
- Audio and video equipment
- Cellular handsets and accessories
- Subscriber Identity Module (SIM) card protection
- Portable electronics
- Communication systems
- 10/100 Mbit/s Ethernet

4.Pinning information



SOT-23



5. Quick reference data

$T_{amb}=25^{\circ}\text{C}$ unless otherwise specified.

Parameter	Symbol	Conditions	Min	Typ	Max	Units
reverse standoff voltage	V_{RWM}				36	V
diode capacitance	C_d	$V_R=0\text{V}$, $f=1\text{MHz}$		17	35	pF

6. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Parameter	Symbol	Conditions	Min	Typ	Max	Units
peak pulse power	P_{PP}	$t_p=8/20\mu\text{s}$ ①②			160	W
peak pulse current	I_{PP}	$t_p=8/20\mu\text{s}$ ①②			2.5	A
junction temperature	T_J				150	$^{\circ}\text{C}$
ambient temperature	T_{amb}		-55		150	$^{\circ}\text{C}$
storage temperature	T_{STG}		-65		150	$^{\circ}\text{C}$

Notes:

- ① Non-repetitive current pulse 8/20 μs exponential decay waveform according to IEC 61000-4-5.
- ② Measured from pin 1 to pin 2.

7. ESD maximum ratings

$T_{amb}=25^{\circ}\text{C}$ unless otherwise specified.

Parameter	Symbol	Conditions	Min	Typ	Max	Units
electrostatic discharge voltage	V_{ESD}	IEC 61000-4-2 (contact discharge) ①②			30	kV
		machine model ②			400	V
		MIL-STD-883 (human body model)			8	kV

Notes:

- ① Device stressed with ten non-repetitive ESD pulses.
- ② Measured from pin 1 to pin 2.



8.ESD standards compliance

Parameter	Conditions
IEC 61000-4-2; level 4 (ESD)	> 15 kV (air); > 8 kV (contact)
MIL-STD-883; class 3 (human body model)	> 4 kV

9.Electrical Characteristic (T_A=25°C unless otherwise noted)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
reverse standoff voltage	V _{RWM}				36	V
reverse leakage current	I _{RM}	V _{RWM} =30V		<0.02	1	μA
breakdown voltage	V _{BR}	I _R =5mA	40	44		V
diode capacitance	C _d	V _R =0V, f=1MHz ①		17	35	pF
clamping voltage	V _{CL}	I _{PP} =1A ①②		55	60	V
differential resistance	r _{dif}	I _{PP} =0.5A			300	Ω


Notes:

① Measured from pin 1 or 2 to pin 3.

② Non-repetitive current pulse 8/20 μs exponential decay waveform according to IEC 61000-4-5.




10.1Typical characteristic





9.SOT-23 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	B	b _p	C	D	E	H _E	A1	L _p
Min	0.95	1.78	0.35	0.08	2.70	1.20	2.20	0.013	0.20
Max	1.40	2.04	0.50	0.19	3.10	1.65	3.00	0.100	0.50



10.Ordering information



yww: Batch Code

Order Code	Package	Base QTY	Delivery Mode
UMW PESD36VS2UT	SOT-23	3000	Tape and reel



13.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.