

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

T.E. PROPRIETARY AND CONFIDENTIAL


This drawing contains proprietary information that shall not be disclosed, duplicated nor used in whole or in part for any purpose other than to evaluate this drawing.

LOC-

DIST-


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		REVISED PER E.O. C8206	110510	-	RB
B		UPDATED PER ECO-14-008850	140506	CB	EA

MASTER KEY



5.

1.220 MAX.



.085 MAX
INSERT PROTRUSION

Ø A

COLOR BAND (BLUE)

B THREAD

EXAMPLE OF PART NUMBER

DTS 26 x xx - xx P/S x-xxxx

MODIFICATION

KEYING POSITION

N = NORMAL, A, B, C, D & E

CONTACT STYLE

P = PIN, S = SOCKET

INSERT ARRANGEMENT

SHELL SIZE

CLASS F = NICKEL

G = NICKEL SPACE GRADE

T = TEFLON NICKEL

W = OLIVE DRAB CADMIUM

Z = ZINC NICKEL

SHELL STYLE

26 = PLUG

CONNECTOR SERIES

DEUTSCH MIL-DTL-38999 SERIES III

6. WHEN MOD -7070 IS SPECIFIED CONNECTORS WILL BE SUPPLIED WITH DEUTSCHCOAT V PLATED CONTACTS AND AN ADDITIONAL WIRE SEALING GROMMET FOR ENHANCED PERFORMANCE.

5. FOUR FLATS FOR SHELL SIZES 9 - 17.
EIGHT FLATS FOR SHELL SIZES 19 - 25.

4. FOR APPLICABLE KEYING DIAGRAM, SEE MIL-DTL-38999.
FOR INSERT ARRANGEMENTS, SEE MIL-STD-1560.

3. GENERAL SPECIFICATIONS: THIS CONNECTOR MEETS THE PERFORMANCE AND INTERMATEABILITY REQUIREMENTS OF MIL-DTL-38999, SERIES III.


2. MATERIAL / FINISH: SHELL - ALUMINUM ALLOY/ SEE PART NUMBER EXAMPLE.
COUPLING RING - ALUMINUM ALLOY/ SEE PART NUMBER EXAMPLE.
RESILIENT INSERTS - SILICONE ELASTOMER.
PLASTIC INSERTS - THERMOPLASTIC.
CONTACTS - COPPER ALLOY/
GOLD PLATED.

1. ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED. THREAD CALLOUTS ARE METRIC.

PART NUMBER	SIZE	Ø A MAX.	B THREAD
DTS26x09-xxP/Sx	09	.858	M12X1.0-6g 0.100R
DTS26x11-xxP/Sx	11	.984	M15X1.0-6g 0.100R
DTS26x13-xxP/Sx	13	1.157	M18X1.0-6g 0.100R
DTS26x15-xxP/Sx	15	1.279	M22X1.0-6g 0.100R
DTS26x17-xxP/Sx	17	1.405	M25X1.0-6g 0.100R
DTS26x19-xxP/Sx	19	1.515	M28X1.0-6g 0.100R
DTS26x21-xxP/Sx	21	1.641	M31X1.0-6g 0.100R
DTS26x23-xxP/Sx	23	1.768	M34X1.0-6g 0.100R
DTS26x25-xxP/Sx	25	1.889	M37X1.0-6g 0.100R

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCH



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.1

2 PLC ±0.01

3 PLC ±0.001

4 PLC ±0.0001

ANGLES ±

FINISH

MATERIAL

TBD

DWN E. ALAWNEH 070411

CHK A. RASMUSSEN 070411

APVD ALEX RENGIFO 110511

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

Customer Drawing

 TE Connectivity

NAME DTS PLUG ENVELOPE

SIZE A2

CAGE CODE -

DRAWING NO. ©DTS26xxx-xxP/Sx

RESTRICTED TO -

SCALE 3.000

SHEET 1 OF 1

REV B

1471-9 (3/11)