


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER ECO-19-009164	24JUN2020	KG	DR



- 1 WIRE RANGE IS FOR 1/0 AWG. STANDARD WIRE CROSS SECTIONAL AREA RANGE: 83,700-119,500 CMA, STRANDED WIRE.
- 2 TERMINAL BODY MATERIAL THK IS 1.778±0.076[.070±.003].
- 3 RECOMMENDED OPERATING TEMP -55°C [131°F] TO +200°C [392°F] FOR HEAT SHRINK TUBING
- 4 HEAT SHRINK TUBING SHELF LIFE OF 18 MONTHS FROM DATE CODE ON LABEL
- 5 TERMINAL BODY PRODUCT SPECIFICATION 108-32046. APPLICATION SPECIFICATION 114-2162.

1	1-1196717-9	HIGH AND LOW TEMPERATURE CROSS LINKED FLUOROPOLYMER HEAT SHRINK TUBING 15.88[.625]MIN IDX44.45±3.05[1.75±.12] RT555-5/8-0-SP
1	323180	TERMINAL BODY: COPPER PER ASTM B152 ANNEALED FINISH: NICKEL PLATE 0.00762 [.000300] MIN EXT THK PER SAE AMS QQ-N-290
-1	PART NO	DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
SEE TABLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± 0.127 [.005]

4 PLC ± -

ANGLES ± 1°

FINISH

SEE TABLE

DWN
JR RUTH
CHK
T MICHELUTTI
APVD
T MICHELUTTI

08DEC09
08DEC09
08DEC09

PRODUCT SPEC
APPLICATION SPEC
WEIGHT

-

CUSTOMER DRAWING

TE Connectivity

NAME
HEAT RESISTANT TERMINAL KIT
WIRE SIZE: 1/0 AWG

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-696647

RESTRICTED TO
-

SCALE
3:1

SHEET
1 OF 1

REV
B