



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		D2	ECR-15-005665	10AUG2015	BDA	PKS

D




C



B


A



- CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 5.59±0.08 [.220±.003] CENTERS.
- SLOT ACCEPTS A SINGLE WIRE MAX OF 0.64-0.81mm [#22-#20] AWG COPPER MAGNET WIRE.
SLOT ACCEPTS A SINGLE WIRE MAX OF 0.72-0.91mm [#21-#19] AWG ALUMINUM MAGNET WIRE
ALUMINUM WIRE RANGE APPLIES FOR POST-TIN PLATED VERSIONS ONLY.
- AFTER INSERTION INTO PLASTIC HOLDER TAB PORTION MUST BE BENT OVER 45° TO 90° OR POTTED-IN TO PREVENT PULL-OUT WHEN MATING RECEPTACLE IS DISCONNECTED.

D

C



1217065

B

1217065-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN	R.GRZYBOWSKI	26FEB98	 TE Connectivity			
			CHK	M.S.FEHER	26FEB98				
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	N.E.NEFF	26FEB98	NAME TERMINAL, TAB 4.75[.187] FASTON™ MAG-MATE™		
		0 PLC ± -		PRODUCT SPEC					
		1 PLC ± -		108-2012					
		2 PLC ± 0.25[.010]		APPLICATION SPEC					
		3 PLC ± -		114-2046					
		4 PLC ± -		SIZE					
		ANGLES ± -		CAGE CODE					
MATERIAL		FINISH		DRAWING NO		RESTRICTED TO			
BRASS		TIN PLATE		A2 00779		C=1217065			
				WEIGHT		-			
				CUSTOMER DRAWING					
				SCALE		10:1			
				SHEET		1 of 1			
				REV		D2			

A