

1.Description

The IRLML2502TR uses advanced trench technology to provide excellent $R_{DS(on)}$ with low gate charge. This device is suitable for use as a load switch or in PWM applications.

2.2Features

- TrenchFET Power MOSFET

2.1Features

- $V_{(BR)DSS}=20V$
- $I_D=4.2A$
- $R_{DS(on)}<45m\Omega(V_{GS}=4.5V)$
- $R_{DS(on)}<80m\Omega(V_{GS}=2.5V)$



3.Application

- Load Switch for Portable Devices
- DC/DC Converter

4.Pinning information

Pin	Symbol	Description
1	G	GATE
2	S	SOURCE
3	D	DRAIN

SOT-23



5.Maximum ratings ($T_A=25^{\circ}C$ unless otherwise noted)

Parameter	Symbol	Rating	Units
Drain-Source Voltage	V_{DS}	20	V
Gate-Source Voltage	V_{GS}	± 12	V
Continuous Drain Current	I_D	4.2	A
Continuous Source-Drain Current(Diode Conduction)	I_S	0.6	A
Power Dissipation	P_D	1.25	W
Thermal Resistance from Junction to Ambient ($t \leq 5s$)	$R_{\theta JA}$	312.5	$^{\circ}C/W$
Junction Temperature	T_J	150	$^{\circ}C$
Storage Temperature	T_{STG}	-55~+150	$^{\circ}C$



6. $T_A=25^{\circ}\text{C}$ unless otherwise specified

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Static						
Drain-source breakdown voltage	$V_{(BR)DSS}$	$V_{GS}=0V, I_D=10\mu A$	20			V
Gate-threshold voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=50\mu A$	0.65		1.2	V
Gate-body leakage	I_{GSS}	$V_{DS}=0V, V_{GS}=\pm 8V$			± 100	nA
Zero gate voltage drain current	I_{DSS}	$V_{DS}=20V, V_{GS}=0V$			1	μA
Drain-source on-state resistance ^a	$R_{DS(ON)}$	$V_{GS}=4.5V, I_D=4.2A$		0.035	0.045	Ω
		$V_{GS}=2.5V, I_D=3.6A$		0.05	0.08	Ω
Forward transconductance ^a	g_{FS}	$V_{DS}=5V, I_D=3.6A$		8		S
Diode forward voltage	V_{SD}	$I_S=0.94A, V_{GS}=0V$		0.76	1.2	V
Dynamic						
Total gate charge	Q_g	$V_{DS}=10V, V_{GS}=4.5V, I_D=3.6A$		4	10	nC
Gate-source charge	Q_{gs}			0.65		
Gate-drain charge	Q_{gd}			1.5		
Input capacitance ^b	C_{iss}	$V_{DS}=10V, V_{GS}=0V, f=1MHz$		300		pF
Output capacitance ^b	C_{oss}			120		
Reverse transfer capacitance ^b	C_{rss}			80		
Switching ^b						
Turn-On Delay Time	$t_{D(on)}$	$V_{DD}=10V$ $R_L=5.5\Omega, I_D\approx 3.6A$ $V_{GEN}=4.5V, R_G=6\Omega$		7	15	ns
Rise Time	t_r			55	80	ns
Turn-Off Delay Time	$t_{D(off)}$			16	60	ns
Fall time	t_f			10	25	ns


Notes :

a. Pulse Test : Pulse width $\leq 300\mu s$, duty cycle $\leq 2\%$.

b. These parameters have no way to verify.




7. Typical Characteristics





8.SOT-23 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	L1	L2	C	D	E	E1	B	B1	θ
Min	1.050	0.000	0.300	0.350	0.100	2.820	1.500	2.700	1.800	0.950	0°
Max	1.150	0.100	0.500	0.550	0.200	3.020	1.700	2.900	2.000	TYP	8°



9.Ordering information



YWW: Batch Code

Order Code	Package	Base QTY	Delivery Mode
UMW IRLML2502TR	SOT-23	3000	Tape and reel



10.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.