








NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0; GREEN
- SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
- NO CONTACTS ON POS. A1 - A3
- THREADED INSERTS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- COLLARS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKED: 3025W3SAM99A30X CONEC ABC

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance			scale: 2:1 (5:1)				
							material: see notes				
				dim. in mm			title: D-SUB COMBINATION FEMALE 25W3S SOLDER CUP with threaded insert				
DO NOT ALTER CAD DRAWING BY HAND				date		name		dwg no: 13K1A4999		DIN-A3 sh: 1	
				drawn	25.06.2015	Heinrich					
				appd.	25.06.2015	Lehmenkühler					
				norm							
				d-old							
											
a	Original										
rev.	description	date	name			part no:		3025W3SAM99A30X			

RoHS compliant