

product type designation

product description

IE FC M12 Plug PRO 4X2

FC M12 plug-in connector in high degree of protection, 8-pin, X-coded

IE FC M12 plug PRO 4x 2; M12 plug-in connector with rugged metal enclosure and FC connection method; with axial cable outlet (X-coded) 1 pack = 1 unit for SCALANCE W and SCALANCE X.



suitability for use

For connecting electrical cables to SCALANCE W (M12 gigabit interface) for fast assembly with the FastConnect system

transfer rate

transfer rate / for Industrial Ethernet

10 Mbit/s, 100 Mbit/s, 1000 Mbit/s, 10000 Mbit/s

interfaces

number of electrical connections

- for Industrial Ethernet FC TP cables
- for network components or terminal equipment

8
1

type of electrical connection

- for Industrial Ethernet FC TP cables
- for network components or terminal equipment

integrated cut-and-clamp contacts for 8-wire TP FC installation cable AWG24 M12 connector (X-coded)

type of electrical connection / FastConnect

Yes

mechanical data

material / of the enclosure

metal

locking mechanism design

Screwed joint

tightening torque / for M12 round connector / maximum

0.6 N·m

connector coding / of the M12 circular connector

X

design, dimensions and weights

type of cable outlet

180° cable outlet

width

17.6 mm

height

17.6 mm

depth

70.7 mm

net weight

48 g

connectable cable cross-section

6.5 ... 8 mm

connectable conductor cross-section

0.21 ... 0.33 mm²

ambient conditions

ambient temperature

- during operation
- during storage
- during transport

-40 ... +85 °C
-50 ... +100 °C
-50 ... +100 °C

chemical resistance

- to water

resistant

protection class IP

IP65/67

product features, product functions, product components / general

product feature

- PoE capability
- PoE+capability
- silicon-free

Yes
Yes
Yes

product component	
• strain relief	Yes
standards, specifications, approvals	
certificate of suitability	
• RoHS conformity	Yes
• UL approval	Yes
• cULus approval	Yes
• railway application in accordance with EN 50155	Yes
standard for structured cabling	Cat6A
further information / internet links	
internet link	
• to web page: selection aid TIA Selection Tool	http://www.siemens.com/tia-selection-tool
• to website: Industrial communication	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Selection guide for cables and connectors	https://sie.ag/2QdlxcP
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAX-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com
last modified:	10/15/2022 