





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B2	DRAFTING ERROR RECTIFICATION	25JUL2017	SV	PKS

- 1 CONTINUOUS STRIP ON REELS WITH TERMINALS
LOCATED ON 8.38±0.08 [.330±.003] CENTERS.
- 2 SLOTTED TERMINAL A SINGLE COPPER MAGNET WIRE
COPPER RANGE: 0.91–1.15mm [#19–#17] AWG.
ALUMINUM RANGE: 0.95–1.15mm [#18.5–#17] AWG.
ALUMINUM WIRE RANGE APPLIES FOR POST-TIN
PLATED VERSIONS ONLY.



1217994-1

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MICHAEL S. FEHER 02OCT2003	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK KURT A. RANDOLPH 02OCT2003				
		APVD KURT A. RANDOLPH 02OCT2003	NAME			
		PRODUCT SPEC	TAB, 4.75 [.187] FASTON,™ 300 SERIES MAG-MATE™			
		APPLICATION SPEC	SIZE		CAGE CODE	DRAWING NO
MATERIAL 4M PRE-MILLED BRASS		FINISH 0.002032 [.000080] MIN TIN PLATE	114-2094		A2 00779	1217994
			WEIGHT 0		RESTRICTED TO —	
			CUSTOMER DRAWING		SCALE 6:1	SHEET 1 of 1
					REV B2	