

1.Description

The ESD5B5VL is a bi-directional TVS (Transient Voltage Suppressor). It is specifically designed to protect sensitive electronic components that may be subjected to ESD (Electrostatic Discharge), EFT (Electrical Fast Transients) and Lightning. It is particularly well-suited for cellular phones, portable device, digital cameras, power supplies and many other portable applications because of its small package and low weight.

3.Features


- Stand-off voltage: $\pm 5V$ Max
- Transient protection for each line according to
IEC61000-4-2 (ESD): $\pm 8kV$ (contact discharge)
IEC61000-4-4 (EFT): 40A (5/50ns)

2.Applications

- Cell phone handsets and accessories
- Personal Digital Assistants (PDAs)
- Notebooks, Desktops, and Servers
- Portable Instrumentation
- Digital Cameras
- MP3/MP4/PMP Players

- IEC61000-4-5 (surge): 3.5A (8/20 μs)
- Capacitance: $C_J = 5pF$ typ.
- Solid-state silicon technology

4.Pinning information



SOD-523



5. Absolute Maximum Ratings

Parameter	Symbol	Rating	Units
Peak pulse power ($t_p = 8/20\mu s$)	P_{PK}	50	W
Peak pulse current ($t_p = 8/20\mu s$)	I_{PP}	3.5	A
ESD according to IEC61000-4-2 air discharge	V_{ESD}	± 15	kV
ESD according to IEC61000-4-2 contact discharge		± 8	kV
Junction temperature	T_J	125	$^{\circ}C$
Operating temperature	T_{OP}	-40 to 85	$^{\circ}C$
Lead temperature	T_L	260	$^{\circ}C$
Storage temperature	T_{STG}	-55 to 150	$^{\circ}C$









6. Electrical Characteristic ($T_A=25^{\circ}\text{C}$ unless otherwise noted)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Reverse stand-off voltage	V_{RWM}				± 5	V
Reverse leakage current	I_R	$V_{RWM}=5\text{V}$			1	μA
Reverse breakdown voltage	V_{BR12}	$I_T=1\text{mA}$	6.5	7.7	8.1	V
Forward voltage	V_{BR21}	$I_F=1\text{mA}$	6.5	7.8	8.1	V
Clamping voltage	V_{CL}	$V_{ESD}=8\text{kV}$		20		V
Clamping voltage	V_C	$I_{pp}=1\text{A}$, $t_p=8/20\mu\text{s}$			10	V
		$I_{pp}=3.5\text{A}$, $t_p=8/20\mu\text{s}$			14	V
Junction capacitance	C_J	$V_R=0\text{V}$, $f=1\text{MHz}$		5	10	pF
		$V_R=5\text{V}$, $f=1\text{MHz}$		2.5	5	pF



7.1Typical characteristic

	
Figure 1: 8/20µs waveform per IEC61000-4-5	Figure 2: Contact discharge current waveform per IEC61000-4-2
	
Figure 3: Clamping voltage vs. Peak pulse current	Figure 4: Capacitance vs. Reverse voltage
	
Figure 5: Non-repetitive peak pulse power vs. Pulse time	Figure 6: Power derating vs. Ambient temperature




7.2Typical characteristic

Figure 7: ESD clamping (+8kV contact discharge per IEC61000-4-2)	Figure 8: ESD clamping (-8kV contact discharge per IEC61000-4-2)



8.SOD-523 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	b _p	C	D	E	H _E	θ
Min	0.58	0.3	0.100	1.15	0.75	1.5	5°
Max	0.68	0.4	0.135	1.25	0.85	1.7	



9.Ordering information



Order Code	Package	Base QTY	Delivery Mode
UMW ESD5B5VL	SOD-523	3000	Tape and reel



10.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.