

SMA Surface Mount Fast Recovery Rectifier

Features

- Low profile package
- Ideal for automated placement
- Glass passivated pallet chip junction
- Super fast reverse recovery time
- Low switching losses, high efficiency
- High forward surge capability

Applications

For use in high frequency rectification and freewheeling application in switching mode converters and inverters for consumer, computer, automotive, and telecommunication




Mechanical Data

- Case: DO-214AC(SMA)
- Molding compound meets UL 94V-0 flammability rating, RoHS-compliant, halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026
- Polarity: Cathode line denotes the cathode end

Function Diagram

Reverse Voltage
50-600 V
Forward Current
2 Ampere

DO-214AC(SMA)







Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	ES2A	ES2B	ES2C	ES2D	ES2E	ES2G	ES2J
Device marking code			ES2A	ES2B	ES2C	ES2D	ES2E	ES2G	ES2J
Maximum Repetitive Peak Reverse Voltage	V _{RRM}	V	50	100	150	200	300	400	600
Maximum RMS Voltage	V _{RMS}	V	35	70	105	140	210	280	420
Maximum DC blocking Voltage	V _{DC}	V	50	100	150	200	300	400	600
Maximum Average Forward Rectified Current @ 60Hz sinewave, Resistance load,TL (Fig.1)	I _{F(AV)}	A	2.0						
Non-repetitive Peak Forward Surge Current @ t=8.3ms Half-sine wave	I _{FSM}	A	50.0						
Storage temperature	T _{stg}	°C	-55 ~+150						
Junction temperature	T _j	°C	-55 ~+150						
Typical Thermal Resistance	R _{θJ-A}	°C /W	65						
	R _{θJ-L}	°C /W	20						

● Electrical Characteristics (Ta=25°C Unless otherwise noted)

PARAMETER	TEST CONDITIONS	SYMBOL	UNIT	ES2A	ES2B	ES2C	ES2D	ES2E	ES2G	ES2J
Maximum instantaneous forward voltage	I _F =2.0A	V _F	V	0.95				1.3		1.7
Maximum reverse recovery time	I _F =0.5A,I _R =1.0A,I _{rr} =0.25A	T _{rr}	ns	35						
Maximum DC reverse current at rated DC blocking voltage	V _R =V _{DC} , T _A =25°C	I _{R1}	μA	5.0						
	V _R =V _{DC} , T _A =125°C	I _{R2}		100						
Typical junction capacitance	4.0V DC,1MHz	C _J	pF	31				17		12

● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)



Ordering Information

Table with 7 columns: PACKAGE, PACKAGE CODE, UNIT WEIGHT(g), REEL(pcs), BOX(pcs), CARTON(pcs), DELIVERY MODE. It lists specifications for SMA packages with codes R2 and R3.

Package Outline Dimensions (SMA/DO-214AC)

Diagram of SMA package outline with dimensions A-H and a table of dimension values in millimeters and inches.

Suggested Pad Layout

Diagram of suggested pad layout with dimensions J, K, M and a table of dimension values in millimeters and inches.