

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

G

14




U

REV PER 0G3A-0256-04

08APR04

JR



TM



STAMPING DETAIL

- △1 FOR 9.14 [.360] MAX WIRE INSULATION DIA
- △2 SUPERSEDED BY 329251
- △3 MATERIAL: BODY; COPPER PER ASTM B152
INSULATION; PVC
COLOR; TRANSLUCENT
- △4 FINISH: BODY; TIN PL. PER ASTM B545

 WIRE RANGE	 Listed	 LR7189 Certified
22-12 AWG STRANDED	22-12 AWG STRANDED	22-12 AWG STRANDED



10000	BOXED	2-329251-2	△2
1500	TAPE MOUNTED	2-329251-1	
1000	LOOSE PIECE	329251	
QTY	DESCRIPTION	PART NO.	
DWN G KRUPER 12/18/92	 Tyco Electronics Corporation Harrisburg, PA 17105		
CHK R HERSEY 12/18/92			
APVD M ELLIS 12/18/92			
PRODUCT SPEC UL 486 C			
APPLICATION SPEC	NAME SPLICE, CLOSED END WIRE SIZE, 22-12 AWG		
—	SIZE	CAGE CODE	DRAWING NO
WEIGHT	—	A3 00779	C-329251
CUSTOMER DRAWING		SCALE	SHEET
		2:1	1 OF 1
		REV	U


AMP INCORPORATED
CUSTOMER SERVICE SYSTEMSMAX RECOMMENDED OPERATING
TEMPERATURE:
105°C MAXFOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTSPRODUCT INFORMATION CENTER
1-800-522-6752FOR APPLICATION
TOOLING INFORMATIONTOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL

- △3

TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± -
1 PLC ± -
2 PLC ± 0.20 [.008]
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH

- △4