


ULTRA FAST RECOVERY RECTIFIER DIODE
FEATURES

- Glass passivated junction
- Low reverse leakage current
- Low forward voltage drop
- High current capability
- Surface Mount device


SMA

MECHANICAL DATA

- Case: SMA(DO-214AC)
- Case Material: Molded Plastic. UL flammability
- Classification Rating: 94V-0
- Weight: 0.065 grams (approximate)

MAXIMUM RATINGS AND CHARACTERISTICS($T_A = 25^{\circ}\text{C}$ unless otherwise noted)

Parameter	Symbol	US2A	US2B	US2D	US2G	US2J	US2K	US2M	Unit
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	50	100	200	400	600	800	1000	V
DC Blocking Reverse Voltage	V _R	50	100	200	400	600	800	1000	V
RMS Reverse Voltage	V _{R(RMS)}	35	70	140	280	420	560	700	V
Maximum Average Forward Rectified Current	I _F	2							A
Non-Repetitive Peak Forward Surge Current @t=8.3ms	I _{FSM}	50							A
Thermal Resistance From Junction To Ambient	R _{θJA}	25							°C/W
Reverse Recovery Time(@I _F =0.5A, I _R =1.0A,I _{RR} =0.25A)	t _{rr}	50				75			nS
Junction Temperature	T _J	-55 ~+150							°C
Storage Temperature	T _{STG}	-55 ~+150							°C

ELECTRICAL CHARACTERISTICS ($T_A = 25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	US2A	US2B	US2D	US2G	US2J	US2K	US2M	Unit	Conditions
Forward voltage	V _F	1.0			1.3	1.7			V	I _F =2A
Reverse current	I _R	5							uA	V _R =V _{RRM} , T _J =25°C
Reverse current	I _R	100							uA	V _R =V _{RRM} , T _J =100°C
Diode capacitance	C _D	50				30			pF	V _R =4V, f=1MHz

Note: Thermal resistance junction to ambient

ULTRA FAST RECOVERY RECTIFIER DIODE

Typical Characteristics

FIG. 1 – FORWARD CURRENT DERATING CURVE




FIG. 2 – MAXIMUM NON-REPETITIVE SURGE CURRENT




FIG.3 – TYPICAL JUNCTION CAPACITANCE







FIG.4-TYPICAL FORWARD CHARACTERISTICS




Notes:

1. Rise Time = 7.0ns max. Input Impedance = 1.0MΩ, 22pF.
2. Rise Time = 10ns max. Input Impedance = 50Ω.




Set time base for 10ns/cm


Fig. 5 Reverse Recovery Time Characteristic and Test Circuit

ULTRA FAST RECOVERY RECTIFIER DIODE
SMA Package Outline Dimensions




Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	2.20	2.80	0.086	0.110
B	1.30	1.70	0.051	0.067
C	4.70	5.30	0.185	0.209
D	1.70	2.55	0.067	0.100
E	0.90	1.50	0.035	0.059
F	0.90	1.50	0.035	0.059

SMA Suggested Pad Layout

Note:

1. Controlling dimension: in millimeters
2. General tolerance: $\pm 0.05\text{mm}$
3. The pad layout is for reference purposes only

ULTRA FAST RECOVERY RECTIFIER DIODE
SMA Tape and Reel
SMA Embossed Carrier Tape


DIMENSIONS ARE IN MILLIMETER										
TYPE	A	B	C	d	E	F	P0	P	P1	W
SMA	2.89	5.35	2.68	Ø1.50	1.75	5.50	4.00	4.00	2.00	12.00
TOLERANCE	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1

SMA Tape Leader and Trailer

SMA Reel


DIMENSIONS ARE IN MILLIMETER								
REEL OPTION	D	D1	D2	G	H	I	W1	W2
7" DIA	Ø178	54.40	13.00	R78	R25.60	R6.50	12.40	17.60
TOLERANCE	±2	±1	±1	±1	±1	±1	±1	±1