



产品承认书

客户名称: 立创商城

产品名称: 圆板陶瓷电容器

规格描述: Y5V-103M/1KV F5*L10

产品编码: JCT82F103M3AF5100A070BFA2

客户料号:

制作日期: 2025-06-12

供应商签署栏			
制作	审核	批准	
邓光彦	张云云	孙洪淇	

客户确认栏			
承认	审核	批准	结论:
			☐ 合格
			☐ 不合格
			☐ 其它:

烦请确认后回传, 以方便交货确认; 未回签表示默认合格, 订货合同按此样品执行交货。

供应商信息:

地址: 东莞市厚街镇三屯村上屯上涌路 28 号 C 栋四楼


电话: +86 769 85885761

传真: +86 769 85885771

邮箱: qe@jk-et.com

网址: <http://www.jk-et.com>

产品承认规格

客户名称	立创商城	日 期	2025-06-12						
产品名称	圆板陶瓷电容器	执行标准	GB/T 2693-2001						
规格描述	Y5V-103M/1KV F5*L10	产品编码	JCT82F103M3AF5100A070BFA2						
客户料号									
1. 温度特性的温度范围		-25℃~+85℃							
2. 工作温度范围		-25℃~+85℃							
3. 外观、印字要求		产品本体表面光洁，无损坏；引脚无氧化，无异物；激光印字清晰、正确、完整。							
4. 印字、尺寸标准(mm)			实测记录						
			D	7.5±1.0	7.60	7.55	7.48	7.50	7.58
			T	2.5±0.8	2.55	2.43	2.40	2.58	2.47
			F	5.0±0.5	5.06	4.96	4.99	4.88	5.00
			L	10.0±1.0	10.23	10.19	10.26	10.10	10.09
			d	0.50±0.05	0.50	0.49	0.50	0.50	0.50
			e	3.0max	1.05	1.26	1.22	1.20	1.00
5. 性能标准			实测记录						
电 容 量	10nF ±20%		10.84	10.12	10.63	11.22	10.54		
损 耗 角	≤0.025		0.0068	0.0070	0.0064	0.0065	0.0068		
耐 电 压	无击穿，无飞弧(2000VDC 60S)		PASS	PASS	PASS	PASS	PASS		
绝缘电阻	≥6000MΩ(500VDC 充电 60S)		PASS	PASS	PASS	PASS	PASS		
材 质	Y5V								
本体包封	蓝色环氧								
测试仪器	ZX6517 容量损耗测试仪 LK2672 耐压测试仪 TH2681A 绝缘电阻测试仪								
测试条件	1KHz 1.0V 25±3℃ 55±30%RH								
6. 环保标准	符合 RoHS2.0 REACH 无卤素标准								
7. 包装标准	散装 1000PCS/包								

How to order for disc ceramic capacitors


①	②	③	④	⑤	⑥	⑦	⑧	⑨	⑩	⑪	⑫
JCT8	2F	103	M	3A	F5	100	A	070	B	F	A2
SERIES	DIELECTRIC	CAPACITANCE CODE	CAPACITANCE TOLERANCE	RATED VOLTAGE	PITCH	LENGTH	LEAD STYLE	DIELECTRIC DIAMETER	COATING	Environmental compliance	Internal control code
JK-ET class II	Y5V	10nF	±20%	1000VDC	5.0mm	10.0mm	Straight	7.0mm	BLUE EPOXY RESIN	RoHS2.0 REACH Halogen free	

Codes for capacitance shall be find expression in three numbers. The first two digits are significant, and the third digit is number of zero.

Performance test


NO	Test item		Performance requirements	Conditions of test
1	Visual examination		No visible damage. Legible marking. Lead frame is not oxidation and its surface is without sundries.	unaided eye or magnifier
2	Dimensions		Dimensional compliance requirements	vernier caliper
3	Marking		Consistent with logo design	unaided eye or magnifier
4	Voltage proof	Between lead wire	No permanent breakdown or flashover during the test period.	test voltage: 2000VDC duration: 60 seconds frequency: 50/60Hz
		Body insulation	No permanent breakdown or flashover during the test period.	test voltage: 2000VAC duration: 60 seconds frequency: 50/60Hz
5	Capacitance		Within specified tolerance. K: ±10% M: ±20%	Temperature: 25±3℃ Humidity: 55±30%RH Voltage: 1.0±0.2V Frequency: 1±0.2KHz
6	Dissipation factor tan δ		Within specified tolerance: Y5P: ≤0.025 Y5U: ≤0.025 Y5V: ≤0.025	Temperature: 25±3℃ Humidity: 55±30%RH Voltage: 1.0±0.2V Frequency: 1±0.2KHz
7	Insulation resistance	Between lead wire	6000MΩ min	Test voltage: 500VDC duration: 60 seconds Frequency: 50/60Hz
		Body insulation	6000MΩ min	Test voltage: 500VDC duration: 60 seconds Frequency: 50/60Hz

■ The constituent parts of capacitor



NO.	constituent	material
①	Coating	Epoxy resin
②	medium	Ceramic
③	Solder	Soldering tin
④	Electrode	Silver oxide
⑤	Lead Frame	CP wire

■ Figure and code of dimension



■ Requirements for concentration limits for certain hazardous substances

Conform RoHS2.0 2011/65/EU, Halogen free, REACH No1907/2006,

PAHS 2005/96/EC, PHTHALATE2005/84/EC

Substances	concentration (unit: ppm)	Substances	concentration (unit: ppm)
Cadmium and cadmium compounds	<100	Cl	<900
Lead and lead compounds	<1000	Br	<900
Mercury and mercury compounds	<1000	Cl+Br	<1500
Hexavalent chromium compounds	<1000	REACH (SVHC)	<1000
PBBS Polubrominated biphenyls	<1000	Benzyl Butyl Phthalate (BBP)	<1000
PBDES Polubrominated diphenylethers	<1000	Di-2-Ethyl Hexyl Phthalate (DEHP)	<1000
Di-butyl Phthalate (DBP)	<1000	Diisobutyl Phthalates (DIBP)	<1000

■ Packing

bulk (1000PCS/bag)

■ Storage conditions

The capacitors are must not store in a corrosive atmosphere, where sulphide or chloride gas, acid, alkali or salt are present. Exposure of the components to moisture, should be avoided. Capacitors can be stored for short periods at any temperature within the entire range of category temperature. For long storage periods, however, the following conditions should be observed:

■ Storage temperature: -25 to +40°C

■ Maximum relative humidity 80%, no dew allowed on the capacitor.

■ Maximum duration 12months.

■ Cautions and warnings

1. Attention is drawn to the fact that repetition of the voltage proof test by the user may damage the capacitor.
2. Do not place the capacitor a PC board whose hole space differs from the specified lead space.
3. Avoid any compressive, tensile or flexural stress.
4. Please consult us first if you wish to embed the capacitor in plastic resins.
5. Do not move the capacitor after it has been soldered to the board.
6. Do not pick up the PC board by the soldered capacitor.