









REV.	ECN NO.	DATE	SIGN	DESCRIPTION



Pin Assignment
Front View



Recommended
Panel Cut-Out

Note:

- * $\varnothing$ Important Dimension.
- * Waterproof Rate: IP67.
- * Housing: Nylon+GF, Black.
- * Male Pin: Copper Alloy, Gold Plated.
- * Shield: Zinc Alloy, Nickel Plated.
- * Screw Nut: Copper Alloy, Nickel Plated.
- * O-Ring: EPDM, Black.
- * For Panel Thickness Max 3.5mm.
- * Nut Torque: 4~6 kgf.cm.

UNIT:mm	TITLE M8 3Pin Panel M Conn. M Pin			ITEM NO 8A-03PMMS-SH7001		DRAWN BY Tony-leng		DATE 2013-10-22	
	SCALE 3:1			DWG NO 8A-03PMMS-SH7001		CHECKED BY Jimmy		DATE 2013-10-22	
	REV. A			CUSTOMER ALTW		APPROVED BY Jerry		DATE 2013-10-22	
	TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°			SHEET 1 OF 1		WC-REV. A.1		QC: Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司