








(5:1)



NOTES:

1. METALSHELLS: STEEL; min. 315µm TIN over 40-80µm NICKEL
2. INSULATORS: PBT GF UL 94 V-0, GREEN
3. SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
4. NO CONTACTS ON POS. A1-A6
5. THREADED INSERTS:
COPPER ALLOY; min. 200µm TIN over 80µm NICKEL
6. COLLARS: COPPY ALLOY; min. 200µm TIN over 80µm NICKEL
7. MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
8. CONNECTOR IS PART MARKED: 3013W6PAM99A30X CONEC ABC

RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH					tolerance		 dim. in mm	scale: 2:1 (5:1)	
								material: SEE NOTES	
						date	name	title: D-SUB COMBINATION MALE 13W6P SOLDER CUP with threaded insert	
					drawn	27.06.16	Henneboel		
					appd.	27.06.16	Lehmenkühler		
					norm				
					d-old				
							dwg no:		DIN-A3
	a	Original					13K1A5234		sh: 1
	rev.	description	date	name			part no: 3013W6PAM99A30X		