

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT - By TE CONNECTIVITY



ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	06APR2017	SV	PKS



- 1 CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 5.59 ± 0.08 [.220 $\pm$.003] CENTERS.
- 2 AFTER INSERTION INTO PLASTIC HOLDER TAB PORTION MUST BE BENT 45° TO 90° OR POTTED-IN TO PREVENT PULL-OUT WHEN MATING RECEPTACLE IS DISCONNECTED.
- 3 SLOTTED TERMINATES SINGLE WIRE ONLY.
COPPER RANGE: 0.65–0.81mm [#22–#20] AWG.
ALUMINIUM RANGE: 0.72–0.91mm [#21–#19] AWG.
- 4 PART IS REELED WITH INTERLAYER PAPER.



2825386-1

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN VIJAI SUBRAMANIAN 17NOV2016	TE Connectivity	
DIMENSIONS: mm[INCHES]		CHK VIJAI SUBRAMANIAN 17NOV2016		
		APVD SENTHIL KUMAR 17NOV16	NAME TAB, 4.75 [.187] FASTON 300 SERIES MAG-MATE	
		PRODUCT SPEC 108-2012		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-2046	SIZE A2	CAGE CODE 00779
MATERIAL BRASS		FINISH TIN PLATED	WEIGHT 0	DRAWING NO C=2825386
		CUSTOMER DRAWING	SCALE 4:1	SHEET 1 OF 1
			REV A	