


AMP

WIRE RANGE


6 AWG
STRADED



- 1 WIRE INSULATION DIA
INSULATION SUPPORT "A" 7.87 [.310] MAX.
- 2 WIRE INSULATION DIA
INSULATION SUPPORT "B" 10.54 [.415] MAX.

INSULATION SUPPORT "A"

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 105° C
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: 600 V MAX
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 10.54-16.77mm ² [20,800-33,100] STRADED
FOR ORDER ENTRY	1-800-526-5142	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.S. GOULDEN 8-30-93	 TE Connectivity				
DIMENSIONS: mm[INCHES]		CHK R. HERSEY 8-30-93					
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD B. BARE 8-30-93	NAME SPLICE, BUTT, SINGLE TO MULTIPLE, TERMINYL, WIRE SIZE: 6 AWG				
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC —					
	APPLICATION SPEC —						
MATERIAL COPPER PER ASTM B-152 NYLON, COLOR:BLUE	FINISH TIN PLATE PER ASTM B-545	WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C-324621	RESTRICTED TO —	
CUSTOMER DRAWING					SCALE NTS	SHEET 1 OF 1	REV F1