




19.57 REF


57.43 REF

3. MATES WITH QSFP28 MSA COMPATIBLE TRANSCEIVER.

5 DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMERS.

 DATUM -A- IS TOP SURFACE OF THE HOST BOARD.

8 DATE CODE (YYWWD) MARKED APPROXIMATELY AS SHOWN




9.72 REF


$$8.90 \pm 0.1 \text{ C}$$

9.70

2.05




0	WITH	2170752-7
1	WITH	2170752-6
0	WITHOUT	2170752-5
1	WITHOUT	2170752-4
2	WITH	2170752-2
2	WITHOUT	2170752-1
# REAR PINS	HEAT SINK OPEN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. 01APR2014 DESIGNER: JASON YANG		 TE Connectivity	
		CHKD: SEAN HAN 30DEC2015 APPROVED:			
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.25 1 PLC ± 0.25 2 PLC ± 0.20 3 PLC ± 0.100 4 PLC ± 0.100 ANGLES $\pm$		NAME: AGE ASSEMBLY, QSFP28 1X1, THRU BEZEL WITH EMI GASKET	
		PRODUCT SPEC: 108-19428 APPLICATION SPEC: 114-32023		SIZE: CASE CODE: DRAWING NO: A100779C-2170752	
MATERIAL: - FINISH: -		WEIGHT: - CUSTOMER DRAWING: -		SCALE: 4:1 SHEET: 1 of 5 REV: A	


2170752-1 AS SHOWN

LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
			-	SEE SHEET 1		-	-	-

HEAT SINK OPEN OPTIONS




WITHOUT HEAT SINK OPEN
SCALE 4:1




WITH HEAT SINK OPEN
SCALE 4:1

OF REAR LEGS OPTIONS




(2.20) (5.00)

2 REAR LEGS VERSION
SCALE 4:1



7.38





1 REAR LEG VERSION
SCALE 4:1



0 REAR LEG VERSION
SCALE 4:1



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: JASON YANG 01APR2014 CHK: SEAN HAN 30DEC2015 APVD: -	TE Connectivity	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.25 1 PLC ±0.25 2 PLC ±0.20 3 PLC ±0.100 4 PLC ± ANGLES ± FINISH -	PRODUCT SPEC 108-19428	NAME CAGE ASSEMBLY, OSFP28 1X1, THRU BEZEL WITH EMI GASKET	
		APPLICATION SPEC 114-32023	SIZE A100779	
MATERIAL -	-	WEIGHT -	DRAWING NO. C=2170752	
Customer Drawing		SCALE 4:1	SHEET 2 OF 5	REV A

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
-	-	SEE SHEET 1		-	-	-	




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JASON YANG 01APR2014	 TE Connectivity	
		CHK SEAN HAN 30DEC2015		
DIMENSIONS:		APVD -	NAME	CAGE ASSEMBLY, OSFP28 1X1, THRU BEZEL WITH EMI GASKET
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-19428	SIZE	CAGE ASSEMBLY, OSFP28 1X1, THRU BEZEL WITH EMI GASKET
	0 PLC ±0.25 1 PLC ±0.25 2 PLC ±0.20 3 PLC ±0.100 4 PLC ±0.100 ANGLES ±°	APPLICATION SPEC 114-32023	DRAWING NO	RESTRICTED TO
MATERIAL	FINISH	WEIGHT	A100779C=2170752	-
-	-	-	Customer Drawing	SCALE 4:1 SHEET 3 OF 5 REV A


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1	-	-	-



RECOMMENDED PCB LAYOUT
SINGLE TYPE OF 1 REAR HOLES OF LEGS
PCB TOLERANCE: ± 0.05
SCALE 6:1



RECOMMENDED PCB LAYOUT
SINGLE TYPE OF 0 REAR HOLES OF LEGS
PCB TOLERANCE: ± 0.05
SCALE 6:1



DETAIL B
SCALE 8:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: JASON YANG 01APR2014	NAME: CAGE ASSEMBLY, OSFP28 1X1, THRU BEZEL WITH EMI GASKET	
DIMENSIONS:		CHK: SEAN HAN 30DEC2015		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	SIZE: CAGE CODE: DRAWING NO: A100779C=2170752	
Ø	0 PLC ± 0.25	108-19428	RESTRICTED TO	
	1 PLC ± 0.25	APPLICATION SPEC	SCALE 4:1 SHEET 4 OF 5 REV A	
	2 PLC ± 0.20			
	3 PLC ± 0.100			
	4 PLC $\pm$			
	ANGLES $\pm$			
	FINISH			
MATERIAL		WEIGHT		
		Customer Drawing		

