

Coaxial Cable Connector 24_MBX-50-2-11/133_N

Description

Straight panel bulkhead cable jack, flange mount

Interface standards
HUBER+SUHNER MBX



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Centre contact	plugged
Outer contact	soldered
Weight	0.005 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	LCP (Liquid crystal polymer)	

Related Documents

Outline drawing	DOU-00254038
Assembly instruction	DOC-0000447993

Ordering Information

Bulk 100 pcs package	24_MBX-50-2-11/133_NH
----------------------	-----------------------

Additional Information

Suitable cables	SUCOFORM_86, MULTIFLEX_86, EZ_86 CU TP M17
-----------------	--

Remarks

Because of the SUCOPLATE body slight discoloration may appear on the solder joint, which has got no influence on the specified technical characteristics of the connector/cable assembly.