






Fig.1 Reel drawing

- Note:
1. Applicable wire is UL3266 AWG#18-#22.
Insulation diameter $\phi 2.1\text{mm}$ max.
 2. Per reel : 6000 contacts.
 3. Applicable crimping machine and crimping conditions (crimp height etc.)
will be specified according to AWG # or wire applied.
 4. Refer to ATAI-E3144 for crimp quality standards.

1	Copper alloy	Contact area : gold plating min. $0.2\mu\text{m}$ Terminal area : tin plating min. $0.5\mu\text{m}$ Others: nickel plating min. $0.5\mu\text{m}$
NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 5 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
				APPROVED : AH. KODAMA	15.07.21	DRAWING NO. EDC-128589-00-00	
				CHECKED : AH. KODAMA	15.07.21	PART NO. MT50B-1822SCFA	
				DESIGNED : KI. KAGOTANI	15.07.21	CODE NO. CL248-0006-3-00	
				DRAWN : KI. KAGOTANI	15.07.21	1/1	