

D

D

C




C

B

B


A


A



- Bemerkungen
NOTES
- 1 Massgebend ist der deutsche Text
ONLY THE GERMAN-LANGUAGE VERSION SHALL BE BINDING
 - 2 Lage des Kontaktpunktes auf der Leiterplatte; Abweichung ± 0.4
POSITION OF CONTACT POINT ON BOARD; DEVIATION ± 0.4
 - 3 Kontaktierung zur Drahtmitte um 0.7mm versetzt
CONTACTING 0.7mm DISPLACED TO WIRE CENTRELINE
 - 4 Kontaktkammer-Nr.
CONTACT CAVITY #
 - 5 FirmenLogo und Leergehäuse-Nr.
ARTWORK LOGO AND HOUSING # (NON LOADED)
 - 6 Kodersteg Vor Erster Kammer
KEYING RIB BEFORE FIRST CAVITY
 - 7 Ausführung nach DIN 60249-2-4
BOARD DESIGN ACCORDING TO DIN 60249-2-4
 - 8 Crimp Kontakt-Nr.:
Material: CuSn4 926770-1, 926917-1
CRIMP CONTACT #: MATERIAL: CuSn4
 - 9 SQUARE HOLE 2X2 mm OPTIONAL LOCKING HOLE $\varnothing 2.5$ mm
 - 10 Kodersteg Nach Letzter Kammer
KEYING RIB AFTER LAST CAVITY

1-1703098-1	MT-EDGE HOUSING	NATURE
PART-NO.:	DESCRIPTION	COLOUR



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Dhanesh	25JUL2013	TE TE Connectivity							
		CHK Dhanesh	25JUL2013								
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD Rajendra	25JUL2013	NAME 4-WAYS MT-EDGE-HOUSING LOOSE PIECE VERSION -					
		PRODUCT SPEC 108-18003									
		APPLICATION SPEC 114-18002									
		WEIGHT -		SIZE A2	CAGE CODE 00779	DRAWING NO C=1703098	RESTRICTED TO -				
MATERIAL PA6.6 / UL94V-2		FINISH		-		Customer Drawing		SCALE 4:1	SHEET 1	OF 1	REV B