









PRODUCT NUMBER
SEE PART NO. TABLE



TOLERANCE: ±0.05
RECOMMENDED P.C.B. Layout
TOP VIEW



NOTES:

1. MATERIAL:
INSULATION(HALOGEN FREE): THERMOPLASTIC HIGH TEMP,UL94V-0,LOW WIRE COMPATIBLE
CONTACT: COPPER ALLOY, t=0.15
2. MATE WITH RECEPTACLE: AFCI 10145492
3. THE INSULATION CAN WITHSTAND IR REFLOW 260°C FOR 10 SECONDS
4. PRODUCT SPEC: GS-12-1444
5. PACKAGING SPEC: GS-14-2616
6. ORDERING CODE: 10144042-XX

NO. OF PINS
02~20 PIN
INSULATION COLOR
PACKAGE
1: TAPE & REEL
2: ESD TAPE & REEL
CONTACT FINISH
1: MATTE-TIN PLATED OVER NICKEL
2: GOLD FLASH OVER NICKEL

mat'l. code				surface	tolerance	projection	product family	
				ISO 1302 ✓	ISO 406 ISO 1101		MINITEK	
ltr	ecm no	dr	date	tolerances unless otherwise specified			title	
A	Rev Release	Tony	2017-05-22	angles	.X±.25		0.8mm Pitch VT Header SMT	
B	ELX-N-33468	Jason	2019-05-14	linear	.XX±.15			
C	ELX-N-35144	Jason	2019-10-22	0°±x°	.XXX±.08		scale 1:1	
				dr	TONY LENG	2017-05-22	dwg no	
				eng	Jason Wang	2019-10-22	sheet 1 of 1	
				chr	-	2019-10-22	10144042	
				appd	TIM YAO	2019-10-22	size	
sheet	revision	C					A3	
index	sheet	1					type Product Customer Drawing	