









AT ALL TIMES WATER RESISTANT CONNECTORS NOT IN USE SHOULD BE COVERED WITH A CONEC WATER RESISTANT CAP OR WATER TIGHT HOOD.



NOTES:

1. METAL SHELLS: COPPER ALLOY; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. CONTACTS: COPPER ALLOY
PLATING: 30µin HARD GOLD over min. 50µin NICKEL
4. THREADED SPACER CLIP: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
PCB-HOLE: $\varnothing 3.1 \pm 0.1$; PCB THICKNESS 1.6mm
5. COLLAR: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
6. FRAME: ZINC DIE CAST; NICKEL PLATED
7. HEXLOCKING SCREW: STAINLESS STEEL
8. RECOMMENDED TORQUE FOR MOUNTING SCREW 35Ncm (3.1 in.LB) / max.40Ncm (3.5 in.LB)
9. CONNECTOR IS PART MARKED: 6STD25SCR99E10X CONEC ABC

Directive 2002/95/EC
„RoHS“
Compliant

„RoHS“
Compliant

Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.

DO NOT ALTER CAD DRAWING BY HAND

				tolerance		 dim. in mm	
					date	name	
				drawn	02.05.08	Lehmenkühler	
				appd.	05.05.08	Mickenbecker	
				norm			
				d-old			
a	Origin						
rev.	description	date	name				



scale:	2:1 (5:1)
material:	SEE NOTES

title:		
D-SUB FEMALE		
25pos. SOLDER PIN STRAIGHT		
threaded spacer clip and hexlocking screw		
dwg no:	Inventor	DIN- A3
15K1A219		sh: 1
part no:		6STD25SCR99E10X

25pos. SOLDER PIN STRAIGHT
aded spacer clip and hexlocking screw

threaded spacer clip and hexlocking screw

dwg no:	Inventor	DIN-
---------	----------	------

15K1A219

sh: 1

part no:	6STD25SCR99E10X
----------	-----------------