


LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APV
			A	RELEASED	08JUN06	RG	SF
			B	REV PER ECO-06-025728	02NOV2006	RG	PD





1. PART NUMBER CHANGES AND OR DESIGN CHANGES AFFECTING
ITEM INTERCHANGEABILITY REQUIRE PRIOR TYCO APPROVAL
AND AUTHORIZATION BY REVISION TO THIS DRAWING.
2. MATERIAL:
- INSULATORS - THERMOPLASTIC, GLASS REINFORCED, COLOR: BLACK
UL94V-0 FLAMMABILITY RATED.
- POWER CONTACTS - PHOSPHOR BRONZE ALLOY,
COPPER ALLOY
- CROWN BANDS - BERYLLIUM COPPER ALLOY
3. FINISH:
- CONTACTS - GOLD PLATE .000030 MIN THK.
.OVER NICKEL .000050 MIN THK.
SOLDER TAILS TIN PLATE .000120 INCH MIN. THK.
OVER NICKEL .000050 MIN THK.

4. ITEMS PROVIDED TO THIS SPECIFICATION TO BE IDENTIFIED ON THE CONTAINER PER THE FOLLOWING IDENTIFIER LABEL

FOLLOWING IDENTIFIER LABEL


		YEAR	WEEK
TYCO PART NO.	DATE CODE	(e.g. 0106)	
XXXXXXX-X	XXXX		



AS SHOWN	1926015-1
DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN R. GRZYBOWSKI CHK S. FLICKINGER APVD S. FLICKINGER		08JUN06 08JUN06 08JUN06		 Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		RIGHT ANGLE SOCKET CONN., HOT PLUG	
		ANGLES FINISH		PRODUCT SPEC		SOLDER TAILS	
MATERIAL		WEIGHT		APPLICATION SPEC		SIZE	RESTRICTED
-		-		-		A200779	C=1926015
CUSTOMER DRAWING						SCALE	1 OF 3
						SHEET	REV D

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
	-	SEE SHEET 1	-	-	-	




PRINTED CIRCUIT LAYOUT
SCALE 5:1

CONNECTOR	CATALOG MODULE #	QTY	SIZE NO.	CONTACT QTY	MATING PIN	MAX. CURRENT (PER CONTACT)	CONTACT SPACING	VOLTAGE RATING
SOCKET	FPI04	2	8	2	1.25 X 7.00 [.049 X .276]	35 amps	7.50 [.2953]	250


THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN R. GRZYBOWSKI 08 JUN 06	tyco Electronics Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK P. DAMATO 08 JUN 06		
		APVD S. ELICKINGER 08 JUN 06	NAME RIGHT ANGLE SOCKET CONN., HOT PLUG SOLDER TAILS	
		PRODUCT SPEC -		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC -	SIZE A200779	
0 PLC ±.5 1 PLC ±.5 2 PLC ±.25 3 PLC ±0.001 4 PLC ±0.0001 ANGLES ±.5		WEIGHT -	CAGE CODE C-1926015	
FINISH -		CUSTOMER DRAWING	RESTRICTED TO -	
		SCALE 4:1	SHEET 2 OF 3	
			REV B	

LOC	DIST	REVISIONS				
GP	00	P	LTR	DESCRIPTION	DATE	APVD
		-		SEE SHEET 1	-	-

P.C. BOARD
SURFACE REF



6. SOLDER TAIL DETAIL
SCALE 10 : 1



7. SOLDER TERMINATION AREA
SCALE 40:1
RECOMMENDED PRINTED CIRCUIT SOLDER HOLE
FINISHED HOLE: Ø1.02 [.040] ±.08 [.003]
DRILLED HOLE: Ø1.15 [.0453] ±.013 [.0005]
COPPER PLATE: .025 [.0010] MIN (PER SURFACE)
TIN PLATE: .008 [.0003] MIN. (PER SURFACE)

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN R. GRZYBOWSKI 08 JUN 06	tyco Electronics Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm[INCHES]		CHK S. FLICKINGER 08 JUN 06	NAME RIGHT ANGLE SOCKET CONN., HOT PLUG	
		APVD S. FLICKINGER 08 JUN 06	SOLDER TAILS	
		PRODUCT SPEC -	SIZE A200779	
MATERIAL -		APPLICATION SPEC -	CAGE CODE C-1926015	DRAWING NO -
FINISH -		WEIGHT -	RESTRICTED TO -	SCALE 4:1
CUSTOMER DRAWING			SHEET 3	OF 3
			REV B	