

RF TERMINATION

Type 6550.41.BB

Description

Standard Termination, Medium Power



Product Configuration

Connector	7/16 jack (female)
Interface standards	IEC 60169-4_CECC 22190_DIN 47223_VG 95250

Technical Data

Electrical Data

Nominal Impedance	50 Ω
Frequency range	0 to 2 GHz
VSWR max.	1.1
Power rating	50 Watt average power up to 25 °C ambient temperature, linearly derated to 0 Watt at 150 °C ambient temperature. 1500 Watt peak power , 5 μ s pulse, 0.05 % duty cycle

Mechanical Data

Weight	0.203 kg
--------	----------

Environmental Data

Operating temperature	-40 °C to 150 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Part	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Silver Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Aluminium	Anodized
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00005435
-----------------	--------------

Ordering Information

Single Packaging	6550.41.BB
Packaging	

Additional Information

Important note	WARNING: Beryllia Ceramic Inside! DO NOT sand, scrap or tamper with. Dispose in accordance with all relevant regulations.
----------------	---

Remarks

50 Watt, if the termination is mounted on an additional heat sink with a max. thermal resistance (R_{th}) of 5 K/Watt. Without additional heat sink this termination is applicable up to 25 Watts only.