


REV.	CHANGE	DATE	APPD.
B	REDRAWN PER ECO 8150	—	—



EPOXY	COLOR: BLACK
LEADWIRES (2)	28 AWG, 7x36 STRANDED, SILVER PLATED COPPER, BLACK TEFLON INSULATION
HOUSING	ALUMINUM
RESISTANCE	10K OHMS AT 25°C ±0.2°C FROM 0°C TO 70°C
R-T CURVE	16
MAX. TEMP.	150°C
INSULATION RESISTANCE	1000 MEGOHMS MINIMUM AT 200 V.D.C.

TOLERANCES UNLESS OTHERWISE NOTED, ALL DIMENSIONS ARE IN INCHES, AND TOLERANCES ARE AS SHOWN HERE. FRACTIONS = ±1/64 DECIMALS .XX = .01 .XXX = .005 ANGLES = 0°30'		DRAWN HS	DATE 8JUN95	FENWAL ELECTRONICS, INC. 450 FORTUNE BOULEVARD, MILFORD, MASSACHUSETTS 01757 U.S.A. TELEPHONE (508) 478 – 6000 FAX (508) 473 – 6035			
		CHECKED	DATE	TITLE PROBE ASSEMBLY OUTLINE			
		APPROVED	DATE				
USED ON		This information is the property of FENWAL ELECTRONICS, INC. It is submitted in confidence, and is not to be disclosed or utilized without written permission.					
SHEET 1	OF 1	DO NOT SCALE DRAWING		SCALE 4:1	SIZE B	DRAWING NUMBER 590–32AD05–103	REV. B