









A1  CODING VARIANT
2. APPLICATION TEMP. -40°C ~140°C

1-2394085-3	M	PLUG ASSEMBLY HVP-HD1000 FINGER ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
			PLUG TPA	M	PA66-GF	AQUA RED		1	1
1-2394085-2	L	PLUG ASSEMBLY HVP-HD1000 FINGER ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
			PLUG TPA	L	PA66-GF	AQUA BROWN		1	1
1-2394085-1	K	PLUG ASSEMBLY HVP-HD1000 FINGER ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
			PLUG TPA	K	PA66-GF	AQUA GREEN		1	1
2394085-9	J	PLUG ASSEMBLY HVP-HD1000 FINGER ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
			PLUG TPA	J	PA66-GF	ORANGE		1	1
2394085-8	H	PLUG ASSEMBLY HVP-HD1000 FINGER ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
			PLUG TPA	H	PA66-GF	YELLOW		1	1
2394085-7	G	PLUG ASSEMBLY HVP-HD1000 FINGER ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
			PLUG TPA	G	PA66-GF	RED		1	1
2394085-6	F	PLUG ASSEMBLY HVP-HD1000 FINGER ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
			PLUG TPA	F	PA66-GF	BROWN		1	1
2394085-5	E	PLUG ASSEMBLY HVP-HD1000 FINGER ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
			PLUG TPA	E	PA66-GF	GREEN		1	1
2394085-4	D	PLUG ASSEMBLY HVP-HD1000 FINGER ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
			PLUG TPA	D	PA66-GF	PURPLE		1	1
2394085-3	C	PLUG ASSEMBLY HVP-HD1000 FINGER ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
			PLUG TPA	C	PA66-GF	BLUE		1	1
2394085-2	B	PLUG ASSEMBLY HVP-HD1000 FINGER ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
			PLUG TPA	B	PA66-GF	NATURE		1	1
2394085-1	A	PLUG ASSEMBLY HVP-HD1000 FINGER ACCESS	PLUG HOUSING	-	PA66-GF	ORNGE	(33)	1	7
			SHIELDING	-	COPPER ALLOY	Ag PLATED		1	6
			CPA - FINGER ACCESS	-	PA66-GF	RED		1	5
			CPA SPRING - FINGER ACCESS	-	STAINLESS STEEL	-		1	4
			HVIL	-	COPPER	Ag PLATED		1	3
			PERIPHERAL SEAL	-	SILICION	-		1	2
			PLUG TPA	A	PA66-GF	BLACK		1	1
TE ASSY NO.	CODE	DESCRIPTION	DESCRIPTION	CODE	MATERIAL	SURFACE COLOR	WEIGHT (g)	QTY	ITEM




FOR FINGER ACCESS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P.LING	26AUG2021	 TE Connectivity	
		CHK J.L.I	26AUG2021		
DIMENSIONS:		APVD I.YIN	26AUG2021	NAME PLUG ASSEMBLY HVP-HD1000	
mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:			
		1 PLC	±0.5	PRODUCT SPEC	
		2 PLC	±0.1	108-160341	
		3 PLC	±0.001	APPLICATION SPEC	
		4 PLC	±0.0001	116-160182	
MATERIAL		5 UNLESS INDICATED		WEIGHT SEE TABLE	
		CUSTOMER DRAWING		SIZE A 00779 C=2394085	
				CAGE CODE 2394085	
				DRAWING NO. A1	
				RESTRICTED TO -	
				SCALE 2:1	
				SHEET 1 OF 3	
				REV A1	



A1
1 CODING VARIANT
2. APPLICATION TEMP. -40°C ~140°C


3-2394085-3	M	PLUG ASSEMBLY HVP-HD1000 TOOL ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
				M	PA66-GF	AQUA RED		1	1
3-2394085-2	L	PLUG ASSEMBLY HVP-HD1000 TOOL ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
				L	PA66-GF	AQUA BROWN		1	1
3-2394085-1	K	PLUG ASSEMBLY HVP-HD1000 TOOL ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
				K	PA66-GF	AQUA GREEN		1	1
2-2394085-9	J	PLUG ASSEMBLY HVP-HD1000 TOOL ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
				J	PA66-GF	ORANGE		1	1
2-2394085-8	H	PLUG ASSEMBLY HVP-HD1000 TOOL ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
				H	PA66-GF	YELLOW		1	1
2-2394085-7	G	PLUG ASSEMBLY HVP-HD1000 TOOL ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
				G	PA66-GF	RED		1	1
2-2394085-6	F	PLUG ASSEMBLY HVP-HD1000 TOOL ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
				F	PA66-GF	BROWN		1	1
2-2394085-5	E	PLUG ASSEMBLY HVP-HD1000 TOOL ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
				E	PA66-GF	GREEN		1	1
2-2394085-4	D	PLUG ASSEMBLY HVP-HD1000 TOOL ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
				D	PA66-GF	PURPLE		1	1
2-2394085-3	C	PLUG ASSEMBLY HVP-HD1000 TOOL ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
				C	PA66-GF	BLUE		1	1
2-2394085-2	B	PLUG ASSEMBLY HVP-HD1000 TOOL ACCESS	FOLLOW 2394085-1 PLUG TPA	-	-	-	(33)	-	2-7
				B	PA66-GF	NATURE		1	1
2-2394085-1	A	PLUG ASSEMBLY HVP-HD1000 TOOL ACCESS	PLUG HOUSING	-	PA66-GF	ORNGE	(33)	1	7
			STAINLESS STEEL	-	COPPER	Ag PLATED		1	6
			CPA - TOOL ACCESS	-	PA66-GF	RED		1	5
			CPA SPRING - TOOL ACCESS	-	STEEL	-		1	4
			HVIL	-	COPPER	Ag PLATED		1	3
			PERIPHERAL SEAL	-	SILICION	-		1	2
			PLUG TPA	A	PA66-GF	BLACK		1	1
TE ASSY NO.	CODE	DESCRIPTION	DESCRIPTION	CODE	MATERIAL	SURFACE COLOR	WEIGHT (g)	QTY	ITEM



FOR TOOL ACCESS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	26AUG2021	TE Connectivity	
		CHK	26AUG2021		
DIMENSIONS:		APVD	26AUG2021	NAME	
mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PLUG ASSEMBLY HVP-HD1000	
		±0.5		SIZE	
		1 PLC ±0.1		CAGE CODE	
		2 PLC ±0.1		DRAWING NO	
		3 PLC ±0.001		RESTRICTED TO	
		4 PLC ±0.0001		A 00779 ©=2394085	
		5 UNLESS OTHERWISE SPECIFIED		SCALE	
				2:1	
				SHEET	
				2 OF 3	
				REV	
				A1	
				CUSTOMER DRAWING	

1A1



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

MATERIAL

DWN
P.L.LING
CHK
J.L.I

APVD
J.L.I

PRODUCT SPEC
108-160341

APPLICATION SPEC
116-160182

WEIGHT
SEE TABLE

CUSTOMER DRAWING

26AUG2021

26AUG2021

26AUG2021

108-160341

116-160182

SEE TABLE

NAME
PLUG ASSEMBLY
HVP-HD1000

SIZE
A

CAGE CODE
00779

DRAWING NO
C=2394085

RESTRICTED TO
-

TE Connectivity

SCALE
2:1

SHEET
3

OF
3

REV
A1