





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	18JUN2020	AJ	SH





2359845-1 AS SHOWN
SCALE 3:1




- 1 MATERIAL:
CAGE ASSEMBLY - 0.25mm THICK STAINLESS STEEL.
EMI SPRINGS - COPPER ALLOY.
HEAT SINK - ALUMINUM
CLIP - STAINLESS STEEL.
- 2 FINISH
EMI SPRINGS - NICKEL PLATING, NON-PLATED EDGES PERMISSIBLE.
HEAT SINK - BLACK ANODIZED
3. MATES WITH SFP-DD MSA COMPLIANT TRANSCEIVERS.
- 4 DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.
5. MINIMUM PC BOARD THICKNESS:
SINGLE SIDED = 1.57 mm
DOUBLE SIDED = 2.20 mm
- 6 REFERENCE APPLICATION SPEC. 114-60027, HOLE A, FOR
RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.
- 7 REFERENCE APPLICATION SPEC. 114-60027, HOLE B, FOR
RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.
8. DATUM -A- IS TOP SURFACE OF THE HOST BOARD.
- 9 MAXIMUM HEIGHT WITH MODULE INSERTED.



2359845-1 AS SHOWN
SCALE 4:1




DETAIL A
SCALE 16:1




23.00	NET WORKING	2359845-3
16.00	SAN	2359845-2
13.70	PCI	2359845-1
DIM.A	APPLICATION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ARTHUR JIN CHK SEAN HAN APVD	16JUL2019 16JUL2019	NAME CAGE ASSEMBLY, SFPDD 1X1 STANDARD, W/ GENERAL HS	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	
mm		0 PLC ±0.25 1 PLC ±0.25 2 PLC ±0.20 3 PLC ±0.10 4 PLC ±0.10 ANGLES ±0.10 FINISH		108-60128	
MATERIAL		- -		APPLICATION SPEC	
-		-		114-60027	
-		-		WEIGHT	
-		-		CUSTOMER DRAWING	
-		-		SIZE CAGE CODE DRAWING NO	
-		-		A100779C=2359845	
-		-		RESTRICTED TO	
-		-		-	
-		-		SCALE 3:1 SHEET 1 OF 5 REV A	


REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
		SEE SHEET 1			




2359845-1 AS SHOWN
W/ PCI HS
SCALE 3:1








2359845-2 AS SHOWN
W/ SAN HS
SCALE 3:1




2359845-3 AS SHOWN
W/ NET WORKING HS
SCALE 3:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: ARTHUR JIN 16JUL2019	 TE Connectivity			
		CHK: SEAN HAN 16JUL2019				
DIMENSIONS: mm 	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.25 1 PLC ±0.25 2 PLC ±0.20 3 PLC ±0.10 4 PLC ±. ANGLES ±. FINISH	APVD: -	NAME	CAGE ASSEMBLY, SFPDD 1X1 STANDARD, W/ GENERAL HS		
		PRODUCT SPEC	-			
		APPLICATION SPEC	-			
		SIZE	A1	CAGE CODE: 2359845		
MATERIAL		WEIGHT	CAGE CODE	2359845	RESTRICTED TO	
-		-	-	-	-	
-		CUSTOMER DRAWING	SCALE	3:1	SHEET 2 OF 5 REV A	


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: ARTHUR JIN 16JUL2019	TE Connectivity	
		CHK: SEAN HAN 16JUL2019		
DIMENSIONS:		APVD: -	NAME: CAGE ASSEMBLY, SFPDD 1X1 STANDARD, W/ GENERAL HS	
mm		PRODUCT SPEC: 108-60128	SIZE: A1	
		APPLICATION SPEC: 114-60027	CAGE CODE: 2359845	
		WEIGHT: -	RESTRICTED TO: -	
MATERIAL: -		CUSTOMER DRAWING	SCALE: 3:1	
			SHEET 3 OF 5	
			REV A	



DETAIL C
SCALE 10:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 16JUL2019 ARTHUR JIN CHK 16JUL2019 SEAN HAN		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±: 1 PLC ±0.25 2 PLC ±0.20 3 PLC ±0.20 4 PLC ±: ANGLES ±:		NAME CAGE ASSEMBLY, SFPDD 1X1 STANDARD, W/ GENERAL HS	
		PRODUCT SPEC 108-60128 APPLICATION SPEC 114-60027		SIZE A 1	
MATERIAL - - -		FINISH - - -		DRAWING NO C=2359845	
WEIGHT -		RESTRICTED TO -		SCALE 3:1	
CUSTOMER DRAWING		SHEET 4 OF 5		REV A	



RECOMMENDED PCB LAYOUT
BELLY TO BELLY
SCALE 6:1

4805 (3/13)