



深圳市兴华鑫电子科技有限公司

Shenzhen xinghuaxin Electronic Technology Co., Ltd

# 承認書

## SPECIFICATION FOR APPROVAL

客戶 (Customer):

客戶料號 (Customer P/N):

興華鑫型號 (Supplier P/N):

XHXDZ-2015 腔体-8  $\Omega$  1W

產品名稱 (Description):

喇叭 (Speaker)

產品規格 (Specification):

| 客戶承認欄<br>(Customer Authorization<br>Signature) | 深圳市興華鑫電子科技有限公司 承認欄<br>(Supplier Audit) |     |     |
|------------------------------------------------|----------------------------------------|-----|-----|
|                                                | 審核                                     | 檢查  | 制作  |
|                                                | 唐国兴                                    | 唐玉来 | 吴银娟 |
| 日期: 2025 年 03 月 21 日                           |                                        |     |     |
| 版次: A                                          |                                        |     |     |

声音让生活更精彩!

地址: 深圳市宝安区新安街道新乐社区新乐路 88 号厂房四层

TEL: 0755-27892904

E-mail: jacky.tang@jsxhxdz.com

Http: [www.jsxhxdz.com](http://www.jsxhxdz.com)

# 深圳市兴华鑫电子科技有限公司


|                                                                                                                                                                                                                                                     |                     |      |            |          |       |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------|------|------------|----------|-------|
| Model No.                                                                                                                                                                                                                                           | XHXDZ-2015 腔体-8Ω 1W | Date | 2025-03-21 | Page No. | 1 / 6 |
| 產品規格內容 (SPECIFICATION)                                                                                                                                                                                                                              |                     |      |            |          |       |
| 1.使用範圍 (Scope)                                                                                                                                                                                                                                      |                     |      |            |          |       |
| 此份規格書是針對多媒體產品內，所使用的微型揚聲器單體所提出的報告。                                                                                                                                                                                                                   |                     |      |            |          |       |
| This specification covers our product of miniature speaker unit for multimedia product.                                                                                                                                                             |                     |      |            |          |       |
| 2.标准测试条件(Test condition)                                                                                                                                                                                                                            |                     |      |            |          |       |
| 一般规格试验状态（特殊要求除外）：常温 5~35℃，常湿 45%~85%，气压 860~1060hPa.                                                                                                                                                                                                |                     |      |            |          |       |
| 判定上有疑问时，试验状态为：温度 20±2℃，相对湿度 60%~70%，气压 860~1060 hPa.                                                                                                                                                                                                |                     |      |            |          |       |
| The test conditions unless otherwise specified should be normal temperature 5 to 35 ℃,Normal humidity 45 to 85% and normal atmospheric pressure 860 to 1060 hPa,However,if there arises a doubt in judgment,the test conditions shall beas follows: |                     |      |            |          |       |
| Temperature 20±2℃                                                                                                                                                                                                                                   |                     |      |            |          |       |
| Humidity 60%~70%                                                                                                                                                                                                                                    |                     |      |            |          |       |
| Atmosphere 860~1060 hPa                                                                                                                                                                                                                             |                     |      |            |          |       |
| 3.電聲特性 (ELECTRO-ACOUSTIC CHARACTERISTICS)                                                                                                                                                                                                           |                     |      |            |          |       |
| 3.1 額定阻抗(Rated Impedance):                                                                                                                                                                                                                          |                     |      |            |          |       |
| 8.0Ω ± 20% (AT 1.6K Hz ,1.0 Vrms)                                                                                                                                                                                                                   |                     |      |            |          |       |
| 3.2 額定輸入功率(Rated Input Power)                                                                                                                                                                                                                       |                     |      |            |          |       |
| 1.0 Watt (At 2.83 Vrms white noise 96 Hours)                                                                                                                                                                                                        |                     |      |            |          |       |
| 3.3 最大輸入功率(Max. Input Power)                                                                                                                                                                                                                        |                     |      |            |          |       |
| 1.2Watt                                                                                                                                                                                                                                             |                     |      |            |          |       |
| 3.4 最低共振頻率(Resonant Frequency)                                                                                                                                                                                                                      |                     |      |            |          |       |
| 1400 Hz ± 20%                                                                                                                                                                                                                                       |                     |      |            |          |       |
| 3.5 輸出音壓(Output S.P.L)                                                                                                                                                                                                                              |                     |      |            |          |       |
| 96± 3dB (0.1Watt , 0.1 Meter. Average at 0.8K,1.0K,1.5K,2.0K Hz)                                                                                                                                                                                    |                     |      |            |          |       |
| 3.6 實效頻率範圍(Frequency Range)                                                                                                                                                                                                                         |                     |      |            |          |       |
| Fo ~ 20KHz (By Output S.P.L. -10dB)                                                                                                                                                                                                                 |                     |      |            |          |       |
| 3.7 失真率(Distortion)                                                                                                                                                                                                                                 |                     |      |            |          |       |
| Less than 5% (At 1.6KHz ,0.89Vrms)                                                                                                                                                                                                                  |                     |      |            |          |       |
| 3.8 工作溫度(Operating Temperature)                                                                                                                                                                                                                     |                     |      |            |          |       |
| -25℃ ~ +65℃                                                                                                                                                                                                                                         |                     |      |            |          |       |
| 3. 9 儲存溫度(Storage temperature)                                                                                                                                                                                                                      |                     |      |            |          |       |
| -25℃ ~ +65℃                                                                                                                                                                                                                                         |                     |      |            |          |       |
| 制 定                                                                                                                                                                                                                                                 | 审 核                 | 核 准  | 文 件 编 号    |          |       |
| 吴银娟                                                                                                                                                                                                                                                 | 唐玉来                 | 唐国兴  |            |          |       |

## 產品規格內容 (SPECIFICATION)

|           |                      |      |            |          |       |
|-----------|----------------------|------|------------|----------|-------|
| Model No. | XHXDZ-2015 腔体-8 Ω 1W | Date | 2025-03-21 | Page No. | 2 / 6 |
|-----------|----------------------|------|------------|----------|-------|

### 4. 可靠性測試 (Reliability Test)

#### 4.1 高低溫差循環測試(Temperature Cycling Test)



|   |                                                            |
|---|------------------------------------------------------------|
| A | Low Temperature (-25°C±3°C)                                |
| B | High Temperature (+65°C±3°C)                               |
| C | Number of Cycle (3 Cycles)                                 |
| D | Duration of Exposure 1 Hours, at Each Temperature Extremes |
| E | Duration of Recovery 1 Hours                               |

#### 4.2 抗濕度試驗(Humidity Test)

|   |                             |                        |
|---|-----------------------------|------------------------|
| A | 相對濕度(Relative Humidity)     | 90-95% at + 40°C ± 3°C |
| B | 測試時間(Durations)             | 96 Hours               |
| C | 恢復時間(Durations of recovery) | 6 Hours                |

#### 4.3 連續負載測試(Load Test)

White Noise Without Weighted Filter 2.83 Volts.(RMS) 100 Hrs.

#### 4.4 跌落試驗(Drop Test)

75 cm Free Falling On Concrete Floor, 10 Times.

#### 4.5 異常音測試(Buzzes & Rattles)

Sine wave between at 2.2Vrms / 200~5000Hz



#### 4.6 極性測試(Polarity test)

Diaphragm Shall Move Forward When Apply a Positive DC. Current to the “+” or “Marked” Terminal.

產品規格內容 (SPECIFICATION)


| Model No. | XHXDZ-2015 腔体-8Ω 1W | Date | 2025-03-21 | Page No. | 3 / 6 |
|-----------|---------------------|------|------------|----------|-------|
|-----------|---------------------|------|------------|----------|-------|

5.測量方式 (Measurement Method)




| Model No. | XHXDZ-2015 腔体-8Ω 1W | Date | 2025-03-21 | Page No. | 4/6 |
|-----------|---------------------|------|------------|----------|-----|
|-----------|---------------------|------|------------|----------|-----|

6. 頻率響應曲線圖(Frequency Response Curve)




7. 阻抗曲線圖(Impedance Curve)



| Model No. | XHXDZ-2015 腔體-8Ω 1W | Date | 2025-03-21 | Page No. | 5 / 6 |
|-----------|---------------------|------|------------|----------|-------|
|-----------|---------------------|------|------------|----------|-------|

8. 喇叭外觀描述

(Unit:mm tolerance:±0.3)



產品規格內容 (SPECIFICATION)

|           |                     |      |            |          |     |
|-----------|---------------------|------|------------|----------|-----|
| Model No. | XHXDZ-2015 腔体-8Ω 1W | Date | 2025-03-21 | Page No. | 6/6 |
|-----------|---------------------|------|------------|----------|-----|

10.包裝示意圖(Packing Standard):

(Unit:cm tolerance:±3)

PACKING STANDARD:

