

Sencity Special Communication Antenna 91121402

Description

Logarithmic-periodic Antenna
Frequency Range 380-520 MHz
Vertical Polarization
Half-power Beam Width 87°
Gain 9dBi



Product Configuration

Technical Data

Electrical Data

	Band 1	Band 2	Band 3
Frequency (MHz)	380 - 410	410 - 470	470 - 520
VSWR	1.5	1.5	1.5
Impedance (Ohm)	50	50	50
Gain (dBi)	9.2	9	8.7
3dB beamwidth (h) (°)	80	85	88
3dB beamwidth (v) (°)	61	60	59
Composite power max (W)	500	500	500
Ambient temperature (°C)	50	50	50

Ports

	Port 1
Connector	7/16, jack (female)
Polarization	vertical
DC grounded	Yes

Connections

	Band 1	Band 2	Band 3
Port 1	X	X	X

General Data

Mechanical Data

Dimensions (mm) 785 x 400 x 400 (Height x Width x Depth)
Weight (kg) 6
Windload frontal: 54 N at 150 km/h, lateral: 150 N at 150 km/h, Wind speed survival: 180 km/h

Packing size (mm): 915x485x485

Connector position Rearside, pointing downwards

Environmental Data

Environmental conditions outdoor
2011/65/EU (RoHS - including compliant
2015/863 and 2017/2102)
WEEE 2012/19/EU no special marking needed
REACH 1907/2006/EC compliant

Scope of supply:

Antenna with weather protective casing for straight connectors.

Sencity Special Communication Antenna 91121402

Attachment:

To tubular masts of 50-380 mm diameter depending on the separate available clamps.

Ice protection:

Due to the very sturdy antenna construction and the protection of the radiating system by the radome, the antenna remains operational even under icy conditions.

Grounding:

All metal parts of the antenna including the mounting kit and the inner conductor are DC grounded.

Material:

All screws and nuts: Stainless steel.

Material Data

Radome colour	white
Radome material	Glass Reinforced Plastic (GRP)

Related Products

738546 Clamp 42-115mm

85010002 Clamp 110-220mm

85010003 Clamp 210-380mm

Order separately.

Related Documents

Mounting instruction	DOC-0000871335
Security instruction	DOC-0000278984
Outline drawing	DOU-00398100

Additional Information

