



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECO-19-009164	24JUN2020	KG	DR



- 1 WIRE RANGE IS FOR 8 AWG. STANDARD WIRE CROSS SECTIONAL AREA RANGE: 13,100-20,800 CMA, STRANDED WIRE
- 2 TERMINAL BODY MATERIAL THK IS 1.219 ± 0.076 [.048 $\pm .003$]
- 3 RECOMMENDED OPERATING TEMP -55°C [131°F] TO +200°C [392°F] FOR HEAT SHRINK TUBING
- 4 HEAT SHRINK TUBING SHELF LIFE OF 18 MONTHS FROM DATE CODE ON LABEL
- 5 TERMINAL BODY PRODUCT SPECIFICATION 108-32046 APPLICATION SPECIFICATION 114-2162

1	8-1190141-0	HIGH AND LOW TEMPERATURE CROSS LINKED FLUOROPOLYMER HEAT SHRINK TUBING 9.53 [.375] MIN ID X 25.400 ± 2.032 [1.000 $\pm .080$] RT555-3/8-0-SP
1	323165	TERMINAL BODY: COPPER PER ASTM B152 ANNEALED FINISH: NICKEL PLATE 0.00762 [.000300] MIN EXT THK PER SAE AMS QQ-N-290
-1	PART NO	DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 30JAN04	TE Connectivity					
DIMENSIONS: mm [INCHES]		CHK MJ SPICER 08APR04						
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127 [.005] 4 PLC ± - ANGLES ± 1°	APVD MJ SPICER 08APR04	NAME - HEAT RESISTANT TERMINAL KIT WIRE SIZE: 8 AWG					
		PRODUCT SPEC - 						
		APPLICATION SPEC - 	SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO -	
		WEIGHT -	A3		00779	C-696633		
MATERIAL SEE TABLE	FINISH SEE TABLE	CUSTOMER DRAWING				SCALE 1:1	SHEET 1 OF 1	REV C