




1. MATERIAL:
BODY: ALUMINUM PER ASTM B317
INSERT: BRASS PER ASTM B36
2. FINISH:
BODY: .000600 MIN MATTE TIN PER ASTM B545
OVER .000060 MIN NICKEL PER ASTM B733.
INSERT: .000150 MIN MATTE NICKEL PER QQ-N-290
3. PTFE DRY LUBRICANT 360 DEGREE ON OUTER DIAMETER OF CRIMP BARREL IN ZONE SHOWN.
4. WIRE INSULATION RANGE: .490-.574.
5. SEE TE CONNECTIVITY APPLICATION SPEC. 114-32098 FOR APPLICATION REQUIREMENTS.
6. SEE TE CONNECTIVITY INSTRUCTION SHEET 408-32087 FOR TOOLING AND CRIMP INSTRUCTIONS, FIGURE 3 FOR WIRE STRIPPING DETAIL.



SCALE 2:1



2102573-1
PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. FABIAN 15NOV2011	 TE Connectivity				
DIMENSIONS: IN		CHK DEBOCK, KIM 28NOV2012					
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD DEBOCK, KIM 28NOV2012	NAME ASSEMBLY, ALUMINUM TERMINAL, STRAIGHT, SINGLE HOLE, 2/0			
	0 PLC ±.1		PRODUCT SPEC				
	1 PLC ±.1		-				
	2 PLC ±.01		APPLICATION SPEC				
	3 PLC ±.005						
	4 PLC ±.0005						
ANGLES ±1°			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
FINISH		WEIGHT	A1	00779	C=2102573		
MATERIAL SEE CALL-OUT		CUSTOMER DRAWING					
SEE CALL-OUT			SCALE	4:1	SHEET	1 OF 1	REV C