

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AF	50		A2	ECR-13-016672	25OCT13	PKSRRP





- 1

SLOT ACCEPTS A 0.54-0.64mm [#23.5-#22] AWG COPPER MAGNET WIRE.
- 2

MATES WITH STANDARD MAG-MATE STYLED POKE-IN TAB TERMINAL.
- 3

WHEN FREE STATE IS COMPRESSED TO 3.23 [.127] DIMENSION GAP BETWEEN SPRING AND CARRIER IS TO BE 0.30 [.012] MAX.
- 4

TIN PLATE OVER NICKEL UNDERPLATE.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 09NOV2006 MICHAEL S. FEHER	TE Connectivity			
DIMENSIONS:		CHK 09NOV2006 KURT A. RANDOLPH				
mm		APVD 09NOV2006 KURT A. RANDOLPH	NAME			
		PRODUCT SPEC	SPECIAL LEAF CONTACT, LOOSE PIECE, 300 SERIES MAG-MATE			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		108-2012	SIZE			
0 PLC ± -		APPLICATION SPEC	CAGE CODE			
1 PLC ± -		114-2046	DRAWING NO			
2 PLC ± 0.25[.010]		WEIGHT -	RESTRICTED TO			
3 PLC ± -		CUSTOMER DRAWING	SCALE 10:1			
4 PLC ± -			SHEET 1 OF 1			
ANGLES ± -			REV A2			
FINISH						
BRASS						