

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	REVISED PER 0720-0044-94	4/27/94	—	DAP
	D1	REVISED PER ECO-17-008808	09MAR2018	RS	DR


AMP WIRE RANGE	 E13288 Listed
22-16 AWG SOLID OR STRANDED	NOT APPLICABLE
 LR7189 Certified	MILITARY P/N AND CLASS
NOT APPLICABLE	NOT APPLICABLE

- 1

STAMP AMP 22-18 APPROX AS SHOWN
22-16 SPLICES ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPEC SAE AS7928
COMMERCIAL WIRE RANGE IS 22-16
- 2

MAXIMUM LENGTH DOES NOT INCLUDE
MANUFACTURING TABS
- 3

WIRE BARREL COLOR CODED ORANGE
TO DENOTE NICKEL MATERIAL



1000	LOOSE PIECE	322324
QUANTITY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN TA BRINKMAN 4-19-93 CHK DA PATTERSON 4-19-93 APVD DE MILLER 4-19-93 PRODUCT SPEC — APPLICATION SPEC — WEIGHT CUSTOMER DRAWING		 TE Connectivity Ltd. NAME SPLICE, BUTT, STANDARD, HIGH TEMPERATURE, STRATO-THERM™, 22-16 AWG SIZE A2 CAGE CODE 00779 DRAWING NO C=322324 RESTRICTED TO —				
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	MAX RECOMMENDED OPERATING TEMPERATURE: 649°C[1200°F] MAX	DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± 0.127[.005] 4 PLC ± — ANGLES ± —	FINISH —	NAME	SPLICE, BUTT, STANDARD, HIGH TEMPERATURE, STRATO-THERM™, 22-16 AWG	SIZE A2	CAGE CODE 00779	DRAWING NO C=322324	RESTRICTED TO —
	FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111										
FOR ORDER ENTRY	1-800-526-5142	WIRE CROSS SECTIONAL AREA RANGE, 0.26-1.65mm²[509-3,206] CIR MILS SOLID OR STRANDED	MATERIAL NICKEL PER ASTM B-162 ANNEALED						SCALE 10:1	SHEET 1 of 1	REV D1	