





DETAIL ”



DETAIL "A"
(TYP.)



ELECTRICAL TESTING

TEST:	NET Z	NET Z
# TURNS	1	1
AWG	—	—
FREQUENCY	1 MHz	5 MHz
NOMINAL	27 Ω	39 Ω
MINIMUM	—	31 Ω
WEIGHT/K	7.24 KGS	

1. COSMETIC SPECIFICATION REFER TO WI-QA-038.

RoHS

CORE DIMENSIONS:

A	$\frac{13.34 \text{ [.525]}}{7.49 \text{ [.295]}}$	$\frac{+}{+}$	$\frac{0.38 \text{ [.015]}}{0.38 \text{ [.015]}}$
B			
C	$\frac{10.30 \text{ [.406]}}{3.81 \text{ [.150]}}$	$\frac{+}{+}$	$\frac{0.30 \text{ [.012]}}{0.13 \text{ [.005]}}$
D			
E	$\frac{5.72 \text{ [.225]}}$	$\frac{+}{+}$	$\frac{0.25 \text{ [.010]}}$

DIMENSIONS ARE IN mm [INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved. 			
				PROJECT/PART NUMBER:	REV	PART TYPE:	DRAWN BY:
				33N0525-500	A	BALUN	WS
				DATE: 04/13/2020	SCALE: 2 : 1	MATERIAL:	
A	NEW RELEASE	04/13/2020	WS	CAD # 33N0525-500-A	TOOL # 0525A	Ferrite	
REV	DESCRIPTION	DATE	INT				