

SUMMARY

Wires

Low	16
High	0
Coax	0
Triax	0
Quad	0
Fiber	0
Fluidic	0



Image is for illustrative purpose only

Download

[Request a quote](#)

[Catalog](#)

Series	C
Termination type	Male solder
IP rating	50
Cable Ø	5.30 - 7.20 mm
Matching parts	CLB.M16.GLLV
Status	active
Alternative part	

TECHNICAL DETAILS

Mechanics

Shell Style/Model	CA*: Straight plug with cable collet and nut for fitting a bend relief
Keying	3 keys (alpha=0, gamma=60; Plug: male contacts; Receptacle: female contacts)
Housing Material	PSU (Polysulfone), gray
Cable Fixing	∅ 5.3 - 7.2 mm
Variant	
Weight	9.07 g

Performance

Configuration	2P.M16 : 16 Low V.
Insulator	
Rated Current	6 Amps

Specifications

Test voltage (kV rms) Contact-contact:	1.5
Air clearance min. (mm) or Creepage distance min. (mm):	0.65


LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Others

- F ret (min): 150 N
- F ret (max): 250 N
- R leak (He) (max): 0.0000001 mbar*l/s (if vacuum-tested)
- Steam sterilization: 20 times (with potting on rear connection)
- IP Rating: 50

DRAWINGS

Draws



Dimensions

	A	L
mm.	18	57
in.	0,71	2,24

RECOMMENDED BY LEMO

Tools

None

Cables

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.