





REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2015/10/09	Mila	Change Rev.01 To Rev.A

360° Adjustable Key Code Direction





Pin Assignments
Front View

UNIT:mm		TOLERANCE ±0.5mm		TITLE M12 B-Code 90° Unshielded Assy 5 Pin F Conn. F Pin		ITEM NO M12B-05BFFB-SR7001		DRAWN BY Mila		DATE 2015-10-09	
SCALE 1:1		SIZE A4		SHEET 1 OF 2		DWG NO M12B-05BFFB-SR7001		CHECKED BY Cary		DATE 2015-10-09	
REV. A		WC-REV. A.1		QC: Inspection item		CUSTOMER ALTW		APPROVED BY Jerry		DATE 2015-10-09	


Amphenol LTW
安費諾亮泰企業股份有限公司

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.



Note:

- * Important Dimension To Check.
- * Waterproof Rate: IP67(Mated)
- * Housing: Nylon,Black
- * Female Pin: Copper Alloy, Gold Plated
- * Female Nut: Zinc Alloy, Nickel Plated
- * Nut: PBT+PC, Black
- * O-Ring: Silicon,Grey
- * Clamp Ring: Nylon,Black
- * Sealing Nut:PBT+PC,Black
- * Seal: Silicon,Grey
- * Seal For Cable OD:Ø4.0mm~Ø7.0mm
- * Screws for Wire connection recommended tightening torque: 0.61~0.84 kgf.cm / 0.059~0.082 N.m
- * Applicable Wire gauge (Stranded wire cross section) 0.14mm² (26AWG) ~ 0.82mm² (18AWG)
- * Mating Recommended tightening torque: 3~4 kgf.cm / 0.29~0.39 N.m
- * Sealing-Nut Recommended tightening torque: 4~6 kgf.cm / 0.39~0.59 N.m
- * Detailed applicable wire specifications may vary depending on the actual wire construction.



UNIT:mm				TITLE M12 B-Code 90° Unshielded Assy 5 Pin F Conn. F Pin			
TOLERANCE				SCALE 1:1	SIZE A4	SHEET 2 OF 2	
±0.5mm				REV. A	WC-REV. A.1	Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	M12B-05BFFB-SR7001	DRAWN BY	Mila	DATE	2015-10-09
DWG NO	M12B-05BFFB-SR7001	CHECKED BY	Cary	DATE	2015-10-09
CUSTOMER	ALTW	APPROVED BY	Jerry	DATE	2015-10-09