


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	REVISED PER E.O. P20044	03NOV2008		RDR
	E	REVISED PER E.O. P20392	03DEC2009		RDR
	F	REVISED PER PCN :E-18-007949	23MAY2018	DD	DM



3

MATERIAL: .010 [0.25] THICK COPPER ALLOY

2.

WIRE RANGE: 22 AWG TO 16 AWG [0.35-1.5 mm²]
INSULATION RANGE: $\varnothing$.075-.125 [$\varnothing$ 1.91-3.18]

1

APPLIES ONLY TO SELECTIVE GOLD 1060-20-0144.
INDICATED DIMENSION SHOWS GOLD PLATED AREA.

NOTES: UNLESS OTHERWISE SPECIFIED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES[mm]

MATERIAL

3

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH

SEE TABLE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN J. APOSTOL 01DEC2009

CHK D. MEYER 02DEC2009

APVD R. REED 03DEC2009

PRODUCT SPEC 0425-015-0000

APPLICATION SPEC 114-151003

WEIGHT 0.16 g

CUSTOMER DRAWING

TE INTERNAL PN 1060-20-0122

DEUTSCH PN 1060-20-0122

PLATING NICKEL

1060-20-0144

1060-20-0144

SELECTIVE GOLD

1060-20-0177

1060-20-0177

TIN

TE Connectivity

NAME STAMPED CONTACT
PIN
SIZE 20

SIZE A3

CAGE CODE 4AFU8

DRAWING NO C-1060-20-01XX

RESTRICTED TO -

SCALE 6:1

SHEET 1 OF 1

REV F