




P	LTR	DESCRIPTION	DATE	DWN	APVD
	E4	REVISED PER ECR-22-126744	20JAN2022	KS	DZ

THE TYPE OF KEYING




SECT A-A

CAVITY MARK-



PUNCHING	1.25
DRILLING	1.4
	A 寸法

RECOMMENDED PCB HOLES




②	HEADER HOISING	6/ 6 NYLON GRASS FILLED
①	TAB	COPPER ALLOY TIN PLATED
NO.	NAME	MATERIAL

— KINK SHAPE:
WITHOUT KINK IS
STRAIGHT SHAPE
OF TINE.

- 1 RECOMMENDED P.C.B LAY OUT.
- 2 APPLICABLE P.C.B. THICKNESS:1.6.
- 3 MATING CONN. P/N
PLUG HOUSING :SEE TABLE.
- 4 PARTS MEET IEC 60335-1 (GWT
GLOW WIRE TEST 750 DEGREE SPEC).
- 5 NYLON 66, GWT, V-0.
- 6 HIGH CURRENT RATING VERSION.

	2-1376392-3	WITH KINK	TYPE C	BLUE	4Pos	2-1376386-6
	1376392-1	WITH KINK	TYPE A	NATURAL	4Pos	1376386-6
	1376392-1	WITHOUT KINK	TYPE A	NATURAL	4Pos	5-1376386-1
	3-1376392-4	WITH KINK	TYPE D	YELLOW	4Pos	3-1376386-4
	2-1376392-3	WITH KINK	TYPE C	BLUE	4Pos	2-1376386-3
	1-1376392-2	WITH KINK	TYPE B	RED	4Pos	1-1376386-2
	1376392-1	WITH KINK	TYPE A	NATURAL	4Pos	1376386-1
	MATING CONN. P/N 	WITH/WTHOUT KINK	TYPE OF KEYING	Color	Pos	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.OISHI 04APR2003		TE Connectivity											
		CHK Y.KASHIWA 28AUG'00													
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLZ ± 0.2 1 PLC ± 2 PLC ± 3/PLC ± 4 PLC ± ANGLES ± 1°		NAME 5.0 POWER KEY CONNECTOR 4P HEADER ASSEMBLY (2ROW)											
															
								PRODUCT SPEC 108-5699							
								APPLICATION SPEC 114-5292							
MATERIAL SEE TABLE		FINISH SEE TABLE		WEIGHT		SIZE A3		CAGE CODE 00779		DRAWING NO C-1376386		RESTRICTED TO —			
CUSTOMER DRAWING										SCALE 3:1		SHEET 1 OF 2		REV F4	

