

Coaxial PCB Connector
85_QMA-S50-0-5/111_N

Description

Right angle PCB jack

Interface Standards
QMA QLF compliant



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 18 GHz

Mechanical Data

Board mounting type surface mount

Environmental Data

Operating temperature -40 °C to 85 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Bronze	SUCOPRO Plating
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	
Fastening nut	Brass	SUCOPRO Plating
Washer	Bronze	SUCOPRO Plating

Related Documents

Outline drawing DOU-00013324
Catalogue drawing DCA-00086813
Mounting hole DOU-00013090

Ordering Information

Bulk 100 pcs package 85_QMA-S50-0-5/111_NH