








HIGH VOLTAGE



LOW VOLTAGE



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
AL	2		A	FIRST ISSUE	16FEB2010	GT
			A1	REVISED PCB HOLES LAYOUT	04APR2011	GT
			A2	REVISED PER ECR-13-009678	18SEP2013	DD

- NOTE:
- 1) TIN PLATED CONTACTS

2) MATERIAL HOUSING PBT, 15%GFF, UL 94 V0

LV-2	LOW-VOLT 7A 42 V DC	293652-5	WHITE
HV-5	HIGH-VOLT 6A 125 V AC	293652-4	WHITE
HV-4	HIGH-VOLT 6A 125 V AC	293652-3	WHITE
HV-3	HIGH-VOLT 6A 125 V AC	293652-2	WHITE
HV-2	SWITCH-KEYING	293652-1	WHITE
KEYING	REMARKS	PART NUMBER	COLOR

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±0.3
2 PLC	±0.1
3 PLC	±
4 PLC	±
ANGLES	±0.5°

MATERIAL

-

FINISH

-

DWN
R. FRABONI

CHK
J. SALO

APVD
L. BATTLO

PRODUCT SPEC
108-20294

APPLICATION SPEC
114-32102

WEIGHT
-

CUSTOMER DRAWING

20JUN2007

11FEB2008

11FEB2008

108-20294

114-32102

-

TE Connectivity

NAME

7.5 mm PCB CONNECTOR ASSEMBLY
90 DEGREE MALE VERSION
FOR USA MARKET

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-293652

-

SCALE

2:1

SHEET

1

OF

1

REV

A2