

2803-4-0000 ✓ ACTIVE

DEUTSCH

TE Internal #: 2803-4-0000

Connector Contacts, Socket, Gold, Gold, 26 – 22 AWG Wire Size, .

14 – .34 mm² Wire Size

[View on TE.com >](#)



Connectors > Rectangular Connectors > Connector Contacts



Contact Type: **Socket**

Contact Mating Area Plating Material: **Gold**

Wire Contact Termination Area Plating Material: **Gold**

Wire Size: **.14 – .34 mm²**

Features

Contact Features

Contact Type	Socket
Contact Mating Area Plating Material	Gold
Wire Contact Termination Area Plating Material	Gold

Dimensions

Wire Size	.14 – .34 mm ²
-----------	---------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2023 (233) SVHC > Threshold: Pb (1% in Contact Lead-Copper Alloy) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free





Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought

TE Part #2562-201-2031L
CONT SOC ASSYTE Part #YDTS24F25-61SNV001
RECP ASSYTE Part #3-1617004-2
B07D692BZ2-0011 - M5757/23-001TE Part #5225395-8
BNC PLUG DUAL CRIMP RG179, 187TE Part #292151-000
B-040-28-NTE Part #ZPF0000000000000545
020-0008-20TE Part #M15570-22-1
TOOL INS/REMTE Part #2804-5-1200
INS SOC ASSYTE Part #2841-5-14300
CONT PINTE Part #YCTL-16C0150000000
JUNCTION ASSY

Documents

Product Drawings

CONT SOC ASSY

English

CAD Files[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2803-4-0000_99.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2803-4-0000_99.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2803-4-0000_99.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.**Datasheets & Catalog Pages**[DEUTSCH Contacts Quick Reference Guide](#)

English