

PRODUCT NUMBER

95278-YXX-XXLF




- RoHS COMPATIBLE, NOTE 6.
- TOTAL NB OF POSITIONS 04 TO 50
- PACKAGING OPTIONS, NOTE 3.
- PIN STYLE SEE SHEET 2
- PLATING SEE SHEET 2

NOTES:

1. HOUSING MAT'L : HIGH TEMPERATURE THERMOPLASTIC. UL94V-0 COLOR: BLACK
2. PIN MATERIAL : PHOSPHOR BRONZE
- 3 - PACKAGING OPTIONS:
 - = POLY BAGS
 - B = TUBE + CAP
 - A = TAPE & REEL WITH CAP, AS AVAILABLE
 - TR = CUSTOM TAPE & REEL WITH CAP, SEE TA840 ONLY FOR P/N 95278-102TR04LF AND P/N 95278-101TR10LF
 - T = TUBE WITHOUT PICK UP CAP
 - K = TAPE & REEL WITHOUT PICK UP CAP, AS AVAILABLE

4. 9N MIN RETENTION IN EITHER DIRECTION
5. TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
6. RoHS COMPATIBLE PRODUCT SPECIFICATIONS

- a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE, 2µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.
- b - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 30 SECONDES IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
- c - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
- d - LEGAL STATEMENT: SEE GS-47-0004



mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family BERGSTIK			
ltr	ecn no	dr	date	tolerances unless otherwise specified					title				
W	F-22120	BVE	15.10.09	angles	linear	x.x ±0.3			UNSHR.HEADER				
X	F-22217	BVE	15.10.19			x.xx ±0.13			DR SMT				
Y	F-23055	AMA	16.01.15			x.xxx ±0.05			scale 5:1				
AA	F-23246	AMA	16.02.12	dr	D.LE		01.01.24		dwg no		sheet 1 of 2	size	
AB	F-23258	AMA	16.02.15	enrg	JM.C		01.01.24		95278		A3		
AC	F-23474	JJU	16.03.08	chr	JM.C		01.01.24						
V	B-20561	AMA	15.03.26	appd	JF.N		01.01.24		type		CUSTOMER	Drawing	
sheet index	revision	AC	U										
	sheet	1	2										

PIN	STYLE	MATING
01		5.9
02		8
03		9.9
04		11.4
05		9.2
06		10.4
07		5.3
09		17.00
10		8.10
11		8.50
12		3.05
13		14.35
14		4.00
15		6.60

PLATING


1 = 0.76µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL

4 = 2µm TIN MIN FULL PLATED

5 = 0.25µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL

8 = 0.38µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL

– 1.27µm NICKEL MIN UNDERLAYER FOR ALL PLATING VERSIONS



mat'l. code				surface	tolerance	projection	product family
				ISO 1302	ISO 406 ISO 1101		BERGSTIK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
N	F08-0253	LMU	08.12.10	angles	linear	mm	UNSHR.HEADER
P	B-18789	LMU	14.09.11				DR SMT
R	B-18983	LMU	14.10.03			scale N/A	
S	B-20276	LMU	15.02.16	dr	D.LE	01.01.24	dwg no
T	B-20561	AMA	15.03.26	enr	JM.C	01.01.24	sheet 2 of -
U	F-22120	BVE	15.10.09	chr	JM.C	01.01.24	size
				appd	JF.N	01.01.24	95278 A3
sheet index	revision sheet						type CUSTOMER Drawing