

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
G	86	P	LTR	DESCRIPTION	DATE	DWN	APVD
			P	REV PER 0G3A-0499-04	24JUN04	JR	MS

- 1 WIRE INSULATION:
- END 'A' 10.80[.425] – 11.94[.470] DIA FOR 1/0 AL
- END 'B' 7.01[.276] – 7.75[.305] DIA FOR 4 CU

△ 2 STAMP 277163-1 AMP 1/0AL-4CU

APPROX AS SHOWN



INSERT & FUNNEL: BRASS MIL-C-50

NICKEL PL QQ-N-290 0.00762[.000300] AVG THK

SPLICE: COPPER ASTM B-187

TIN PL ASTM B545 0.00381[.000150] MIN THK

MATERIAL & FINISH

277163-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM		7/6/89		tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608							
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK MS FEHER		5/1/91		NAME WIRE SPLICE, TRANSITIONAL, COPALUM, SEALED, WIRE SIZE: 22.0mm [4] COPPER 55.5mm ² [1/0] ALUMINUM					
		APVD MJ SPICER		5/1/91									
		PRODUCT SPEC 108-11011											
		APPLICATION SPEC 114-2134											
MATERIAL SEE TABLE		FINISH SEE TABLE		WEIGHT 92.5 GRAMS		SIZE A2		CAGE CODE 00779		DRAWING NO C=277163		RESTRICTED TO —	
				CUSTOMER DRAWING		SCALE 2:1		SHEET 1 OF 1		REV P			